

# Inductive sensor

### NRN10-12GM40-E2-IO-C

- 10 mm non-flush
- Reduction factor = 1
- Magnetic field resistant
- Weld Immune
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set




### **Function**

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.


### **Dimensions**



### **Technical Data**


General specifications		
Switching function		Normally open/closed (NO/NC) programmable
Output type		PNP
Rated operating distance	Sn	10 mm (factory setting)
Near operating distance		8 mm (can be activated by software)
Installation		non-flush
Output polarity		DC
Assured operating distance	Sa	0 8.1 mm
Reduction factor r <sub>Al</sub>		1
Reduction factor r <sub>Cu</sub>		1

Technical Data		
Reduction factor r <sub>304</sub>		1
Reduction factor r <sub>St37</sub>		1
Output type		3-wire
Nominal ratings		
Operating voltage	$U_B$	10 30 V DC
Switching frequency	f	0 1300 Hz (switch point mode) 0 80 Hz (window mode, switch point mode with stability alarm)
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	$U_d$	≤ 0.5 V
Operating current	ΙL	0 200 mA
Off-state current	l <sub>r</sub>	0 0.5 mA typ. 60 μA at 25 °C
No-load supply current	I <sub>0</sub>	≤ 15 mA
Time delay before availability	$t_v$	max. 150 ms
Constant magnetic field	В	200 mT
Alternating magnetic field	В	200 mT
Status indicator		LED yellow
Functional safety related parameters		•
MTTF <sub>d</sub>		362 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0%
nterface		
Interface type		IO-Link ( via C/Q )
IO-Link revision		1.1
Device ID		0x201114 (2101524)
Transfer rate		COM2 (38.4 kBaud)
Min. cycle time		2.3 ms
Process data width		
		Process data input (control system side): 2 Bit Process data output (control system side): none
SIO mode support		yes
Compatible master port type		A
Compliance with standards and directives		
Standard conformity		FN 000 (F 5 0 000 F
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
Approvals and certificates		
Protection class		II
Rated insulation voltage	$U_{i}$	60 V
Rated impulse withstand voltage	$U_{imp}$	800 V
UL approval		cULus Listed, General Purpose Class 2 power source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
lechanical specifications		
Connection type		cable PUR, 2 m
Core cross section		0.34 mm <sup>2</sup>
Housing material		Brass, PTFE coated
Sensing face		PPS
Degree of protection		IP67
Cable		



Cable diameter	$4.3 \text{ mm} \pm 0.1 \text{ mm}$
Bending radius	> 10 x cable diameter
Mass	78 g
Factory settings	
Default setting	operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 10 mm
General information	
Scope of delivery	2 self locking nuts in scope of delivery

## Connection



# **Function Principle**

#### Switching output modes


Switch point mode at rated operating distance  $\mathbf{s}_{\mathbf{n}}$ 

Switch point 2 SP 2 (rated operating distance  $s_{n}$ )



Switch point mode with near operating distance

Switch point 1 SP1 (near operating distance)




#### Window mode

Switch point 2 SP 2 (rated operating distance  $\mathbf{s}_{n)}$ Switch point 1 SP1 (near operating distance) Normally open Normally closed


# Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance  $s_n$ )



### **Accessories**

	BF 12	Mounting flange, 12 mm
Ho.	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs
	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs
	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
	ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals
8	ICE3-8IOL-K45S-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
S. C.	IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection
	ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs
0 (a) 0 (a) 0 (a) 0 (a) 11 (a) 0 (a)	ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs
	ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors