Release date: 2022-07-13 Date of issue: 2022-07-13 Filename: 306533-0009_eng.pdf



Inductive sensor

NRB15-30GM50-E2-IO-C-V1

- 15 mm flush
- Reduction factor = 1
- Magnetic field resistant
- Weld Immune
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set




Function

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

Dimensions



Technical Data

General specifications		
Switching function		Normally open/closed (NO/NC) programmable
Output type		PNP
Rated operating distance	Sn	15 mm (factory setting)
Near operating distance		10 mm (can be activated by software)
Installation		flush
Output polarity		DC
Assured operating distance	Sa	0 12.15 mm
Reduction factor r _{Al}		1
Reduction factor r _{Cu}		1


Reduction factor r ₃₀₄		1
Reduction factor r _{St37}		1
Output type		3-wire
lominal ratings		
Operating voltage	U_B	10 30 V DC
Switching frequency	f	0 600 Hz (switch point mode) 0 25 Hz (window mode, switch point mode with stability alarm)
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_{d}	≤ 0.5 V
Operating current	ΙL	0 200 mA
Off-state current	l _r	$0 \dots 0.5$ mA typ. $60~\mu A$ at $25~^{\circ} C$
No-load supply current	I ₀	≤ 15 mA
Time delay before availability	t_{v}	max. 150 ms
Constant magnetic field	В	200 mT
Alternating magnetic field	В	200 mT
Status indicator		Multihole-LED, yellow
Functional safety related parameters		
MTTF _d		362 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
nterface		
Interface type		IO-Link (via C/Q = pin 4)
IO-Link revision		1.1
Device ID		0x201113 (2101523)
Transfer rate		COM2 (38.4 kBit/s)
Min. cycle time		2.3 ms
Process data width		Process data input (control system side): 2 Bit Process data output (control system side): none
SIO mode support		yes
Compatible master port type		A
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
Approvals and certificates		
Protection class		II
Rated insulation voltage	Ui	60 V
Rated impulse withstand voltage	U _{imp}	800 V
UL approval		cULus Listed, General Purpose Class 2 power source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		Connector plug M12 x 1 , 4-pin
Housing material		Brass, PTFE coated
Sensing face		PPS
Degree of protection		IP67
Mass		156 g
Factory settings		



General information

Scope of delivery 2 self locking nuts in scope of delivery

Connection



Connection Assignment



Wire colors in accordance with EN 60947-5-2

1 | BN (brown) 2 | WH (white) 3 | BU (blue) 4 | BK (black)


Switching output modes

Switch point mode at rated operating distance $\boldsymbol{s}_{\boldsymbol{n}}$

Switch point 2 SP 2 (rated operating distance s_{n)}



Switch point mode with near operating distance




Window mode

open

Switch point 2 SP 2 (rated operating distance $\boldsymbol{s}_{\boldsymbol{n})}$ Switch point 1 SP1 (near operating distance) Normally Normally

Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance s_n) Switch point 1 SP1 (near operating distance) Normally open ____ Normally closed

Accessories

BF 30	Mounting flange, 30 mm
V1-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Accessories

V1-W-2M-PUR Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors