Release date: 2023-05-09 Date of issue: 2023-05-09 Filename: 304276-000038_eng.pdf

Inductive sensor

NSB10-30GH50-2E2-V1-S2D2


- No unusable area
- 10 mm flush
- Use of standard metallic actuating surfaces
- Applications up to Cat. 2, PLd/SIL 2 possible (can be used redundantly up to Cat. 3, PLe/SIL 3)
- LED for switching state and fault indication
- Safety outputs OSSD
- TÜV certified
- high-grade steel housing V4A/316L



Function

The inductive safety sensors are TÜV-certified in accordance with the EU Machinery Directive, Performance Level PLd, Category 2, and SIL2. They are used to safeguard machines and plant components, as well as for reliable position detection in this environment. With their OSSD interface for reliable, redundant shutdown of electronic outputs, they enable easy connection to a safety PLC or fail-safe control interfaces. They can also be operated as standard sensors. The sensors reliably detect standard metal objects in front of the sensor face without coding or similar; there is no blind zone. High characteristic safety values allow longer testing intervals than comparable solutions with a microcontroller. 2 sensors can be connected with 2-channel redundancy and allow PLe as a Category 3 solution.

Dimensions



Technical Data

General specifications		
Switching function		2 x normally open (NO)
Output type		PNP
Rated operating distance	Sn	10 mm
Installation		flush
Output polarity		DC
Assured operating distance	Sa	0 8.1 mm
Actuating element		Reference target according EN IEC 60947-5-2 (FE360 - ST37K) 30 mm x 30 mm x 1 mm
Reduction factor r _{Al}		0.5
Reduction factor r _{Cu}		0.45



Technical Data		
Reduction factor r ₃₀₄		0.8
Reduction factor r _{Brass}		0.55
Output type		4-wire
Nominal ratings		
Operating voltage	U _B	18 30 V
Rated operating voltage	U _e	24 V
Switching frequency	f	0 30 Hz
Hysteresis	H	typ. 5%
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Overload resistance		yes
Voltage drop	U_{d}	≤3 V
Poted inculation voltage		at I _L (sum of all outputs) max. 50 mA 30 V
Rated insulation voltage	U _{BIS}	
Operating current	l _L	1 30 mA per output
Off-state current	l _r	0 0.5 mA
No-load supply current	l ₀	≤ 15 mA
Time delay before availability	t _v	≤ 300 ms
Switching state indicator		LED, yellow
Error indicator		LED, red
Functional safety related parameters		SIL 2
Safety Integrity Level (SIL)		
Performance level (PL)		PL d Cat. 2
Category		
MTTF _d		> 7500 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)	0	min. 60 %
Assured release distance of a PDDB	S _{ar}	15 mm
Compliance with standards and directives		
Standard conformity		EN 150 000 (5 5 0 000 5
Standards		EN IEC 60947-5-2:2007 EN IEC 60947-5-3:2013 EN ISO 13849-1:2015 EN IEC 61508:2010 EN 62061:2005+AC:2010+A1:2013+A2:2015 compatible with EN ISO 61131-2:2007 Typ 1, 2, 3
Approvals and certificates		
UL approval		cULus Listed, General Purpose, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Altitude		≤ 2000 m above MSL
Mechanical specifications		
Connection type		Connector plug M12 x 1 , 4-pin
Housing material		Stainless steel 1.4404 / AISI 316L
Sensing face		PBT
Degree of protection		IP68 / IP69
Mass		108 g
IVIGOS		108 g
General information		108 g

OSSD1/

Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Commissioning

Note for Setting the Safety Control
The sensor has a self-monitoring function for the outputs. Therefore, to avoid any malfunctions of the sensor, deactivate all test pulses of the connected safety controller to the sensor.

Accessories

	BF 30	Mounting flange, 30 mm
	V1-G-S-BK2M-PUR-A- V1-G	Cordset M12 socket yellow straight to M12 plug yellow straight A-coded, 4-pin, PUR cable weld spatter resistant black, UL approved, drag chain suitable, torsion resistant
66	V1-W-S-BK2M-PUR-A- V1-G	Cordset M12 socket yellow angled to M12 plug yellow straight A-coded, 4-pin, PUR cable weld spatter resistant black, UL approved, drag chain suitable, torsion resistant