Release date: 2022-05-30 Date of issue: 2022-05-30 Filename: 306533-0021_eng.pdf

TEPTED 1-150E THE PER SERVICE STATE OF THE PE

Inductive sensor

NRB15-30GS50-E2-IO-V1

- 15 mm flush
- Reduction factor = 1
- Magnetic field resistant
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set




Function

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

Dimensions



Technical Data


General specifications		
Switching function		Normally open/closed (NO/NC) programmable
Output type		PNP
Rated operating distance	Sn	15 mm (factory setting)
Near operating distance		10 mm (can be activated by software)
Installation		flush
Output polarity		DC
Assured operating distance	Sa	0 12.15 mm
Reduction factor r _{Al}		1
Reduction factor r _{Cu}		1

Technical Data		
Reduction factor r ₃₀₄		1
Reduction factor r _{St37}		1
Output type		3-wire
Nominal ratings		O WIIC
Operating voltage	U _B	10 30 V DC
Switching frequency	f f	0 600 Hz (switch point mode)
		0 25 Hz (window mode, switch point mode with stability alarm)
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_d	≤ 0.5 V
Operating current	IL	0 200 mA
Off-state current	l _r	0 0.5 mA typ. 60 μA at 25 °C
No-load supply current	I ₀	≤ 15 mA
Time delay before availability	t _v	max. 150 ms
Constant magnetic field	В	200 mT
Alternating magnetic field	В	200 mT
Status indicator		Multihole-LED, yellow
Functional safety related parameters		
MTTF _d		362 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Interface		
Interface type		IO-Link (via C/Q = pin 4)
IO-Link revision		1.1
Device ID		0x201003 (2101251)
Transfer rate		COM2 (38.4 kBaud)
Min. cycle time		2.3 ms
Process data width		Process data input (control system side): 2 Bit Process data output (control system side): none
SIO mode support		yes
Compatible master port type		A
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
Approvals and certificates		
Protection class		II
Rated insulation voltage	Ui	60 V
Rated impulse withstand voltage	U _{imp}	800 V
UL approval	- imp	cULus Listed, General Purpose Class 2 power source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		Connector plug M12 x 1, 4-pin
Housing material		Stainless steel 1.4305 / AISI 303
Sensing face		PBT
Degree of protection		IP67
Mass		153 g



Default setting	operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 15 mm
General information	
Scope of delivery	2 self locking nuts in scope of delivery

Connection



Connection Assignment




Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Switching output modes

Switch point mode at rated operating distance $\boldsymbol{s}_{\boldsymbol{n}}$

Switch point 2 SP 2 (rated operating distance s_{n)}



Switch point mode with near operating distance

Switch point 1 SP1 (near operating distance)

Window mode


Normally open

Normally closed

Switch point 2 SP 2 (rated operating distance $\boldsymbol{s}_{\boldsymbol{n})}$ Switch point 1 SP1 (near operating distance) Normally Normally

Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance s_{n)} Switch point 1 SP1 (near operating distance) Normally open ____ Normally closed

Accessories



Accessories V1-W-2M-PVC Female cordset, M12, 4-pin, PVC cable ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs

EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors

Ethernet IO-Link module with 8 inputs/outputs

ICE1-8IOL-G60L-V1D

ICE2-8IOL-K45P-RJ45