

# Inductive sensor

## NSN15-30GM50-2E2-V1-M1-S2D2


- No unusable area
- 15 mm non-flush
- Use of standard metallic actuating surfaces
- Applications up to Cat. 2, PLd/SIL 2 possible (can be used redundantly up to Cat. 3, PLe/SIL 3)
- LED for switching state and fault indication
- Safety outputs OSSD
- E1-Type approval
- Extended temperature range
- -40 ... +85 °C
- TÜV certified

# 

#### **Function**

The inductive safety sensors are TÜV-certified in accordance with the EU Machinery Directive, Performance Level PLd, Category 2, and SIL2. They are used to safeguard machines and plant components, as well as for reliable position detection in this environment. With their OSSD interface for reliable, redundant shutdown of electronic outputs, they enable easy connection to a safety PLC or fail-safe control interfaces. They can also be operated as standard sensors. The sensors reliably detect standard metal objects in front of the sensor face without coding or similar; there is no blind zone. High characteristic safety values allow longer testing intervals than comparable solutions with a microcontroller. 2 sensors can be connected with 2-channel redundancy and allow PLe as a Category 3 solution.

#### Dimensions



### **Technical Data**

General specifications		
Switching function		2 x normally open (NO)
Output type		PNP
Rated operating distance	Sn	15 mm
Installation		non-flush
Output polarity		DC
Assured operating distance	Sa	0 12.15 mm
Actuating element		Reference target according EN IEC 60947-5-2 (FE360 - ST37K) 45 mm x 45 mm x 1 mm
Reduction factor r <sub>AI</sub>		0.5

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Technical Data		
Reduction factor r <sub>Cu</sub>		0.5
Reduction factor r <sub>304</sub>		0.8
Reduction factor r <sub>Brass</sub>		0.55
Output type		4-wire
Nominal ratings		
Operating voltage	UB	18 30 V
Rated operating voltage	Ue	24 V
Switching frequency	f	0 20 Hz
Hysteresis	H	typ. 5%
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Overload resistance Voltage drop	U <sub>d</sub>	yes ≤ 3 V at I <sub>L</sub> (sum of all outputs) max. 50 mA
Rated insulation voltage	U <sub>BIS</sub>	30 V
Operating current	IL	1 30 mA per output
Off-state current	- Ir	0 0.5 mA
No-load supply current	l <sub>o</sub>	≤ 15 mA
Time delay before availability	t <sub>v</sub>	≤ 300 ms
Switching state indicator	-v	LED, yellow
Error indicator		LED, red
Functional safety related parameters		
Safety Integrity Level (SIL)		SIL 2
Performance level (PL)		PLd
Category		Cat. 2
MTTF <sub>d</sub>		> 7500 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		min. 60 %
Assured release distance of a PDDB	S <sub>ar</sub>	22.5 mm
Compliance with standards and directives	Jar	22.5 mm
Standard conformity		
Standards		EN IEC 60947-5-2:2007 EN IEC 60947-5-3:2013 EN ISO 13849-1:2015 EN IEC 61508:2010 EN 62061:2005+AC:2010+A1:2013+A2:2015 compatible with EN ISO 61131-2:2007 Typ 1, 2, 3
Approvals and certificates		
UL approval		cULus Listed, General Purpose, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
E1 Type approval		10R-06
Ambient conditions		
Ambient temperature		-40 85 °C (-40 185 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Altitude		≤ 2000 m above MSL
Mechanical specifications		
Connection type		Connector plug M12 x 1 , 4-pin
Housing material		brass, nickel-plated
Sensing face		PBT
Degree of protection		IP68 / IP69
Mass		108 g
General information		•
Scope of delivery		2 self locking nuts in scope of delivery

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

#### **Connection**



#### **Connection Assignment**



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

#### Commissioning

Note for Setting the Safety Control The sensor has a self-monitoring function for the outputs. Therefore, to avoid any malfunctions of the sensor, deactivate all test pulses of the connected safety controller to the sensor.

Accessories						
	BF 30	Mounting flange, 30 mm				
e e	V1-G-S-BK2M-PUR-A- V1-G	Cordset M12 socket yellow straight to M12 plug yellow straight A-coded, 4-pin, PUR cable weld spatter resistant black, UL approved, drag chain suitable, torsion resistant				
6	V1-W-S-BK2M-PUR-A- V1-G	Cordset M12 socket yellow angled to M12 plug yellow straight A-coded, 4-pin, PUR cable weld spatter resistant black, UL approved, drag chain suitable, torsion resistant				

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3