

Inductive sensor

NRB20-L3-E2-IO-V1

- 20 mm flush
- Reduction factor = 1
- Magnetic field resistant
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set
- 4-way LED indicator
- Quick mounting bracket




Function

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

Dimensions



Technical Data

General specifications		
Switching function		Normally open/closed (NO/NC) programmable
Output type		PNP
Rated operating distance	s_n	20 mm (factory setting)
Near operating distance		15 mm (can be activated by software)
Installation		flush
Output polarity		DC



Technical Data Assured operating distance 0 ... 16.2 mm Reduction factor rAI Reduction factor r_{Cu} Reduction factor r₃₀₄ 1 Reduction factor r_{St37} Output type 3-wire **Nominal ratings** Operating voltage U_B 10 ... 30 V DC 0 ... 440 Hz (switch point mode) 0 ... 10 Hz (window mode, switch point mode with stability alarm) Switching frequency typ. 3 % Hysteresis reverse polarity protected Reverse polarity protection Short-circuit protection pulsing ≤ 0.5 V Voltage drop U_{d} Operating current I_{L} 0 ... 200 mA Off-state current 0 ... 0.5 mA typ. 60 μA at 25 °C No-load supply current I_0 ≤ 20 mA Time delay before availability max. 150 ms t_v Constant magnetic field В 200 mT R 200 mT Alternating magnetic field Operating voltage indicator LED, green Status indicator LED, yellow Functional safety related parameters 701 a $MTTF_d$ Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0% Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision Device ID 0x201001 (2101249) Transfer rate COM2 (38.4 kBaud) Min. cycle time Process data width Process data input (control system side): 2 Bit Process data output (control system side): none SIO mode support yes Compatible master port type Α Compliance with standards and directives Standard conformity Standards EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012 Approvals and certificates Protection class Ш Rated insulation voltage Ui 60 V U_{imp} 800 V Rated impulse withstand voltage **UL** approval cULus Listed, General Purpose Class 2 power source CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** Ambient temperature -25 ... 70 °C (-13 ... 158 °F) Storage temperature -40 ... 85 °C (-40 ... 185 °F) **Mechanical specifications** Connector plug M12 x 1, 4-pin Connection type GD-ZnAl4Cu1, coated Housing material

mounting flange PA6-GF35


Technical Data

205 g

Factory settings

operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 20 mm Default setting

Connection



Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Function Principle


Switching output modes

Switch point mode at rated operating distance $\boldsymbol{s}_{\boldsymbol{n}}$

Switch point 2 SP 2 (rated operating distance s_{n)}



Switch point mode with near operating distance



Window mode

Switch point 2 SP 2 (rated operating distance s_{n)}


Switch point 1 SP1 (near operating distance)

Normally open

Normally closed


Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance s_n)



Accessories

V1-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey
V1-W-2M-PVC	Female cordset, M12, 4-pin, PVC cable

Accessories MHW 01 Modular mounting bracket MH 02-L Mounting aid for VariKont-L MH 04-2681F Mounting aid for VariKont, +U1+ and +U9* ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors