




Function

The inductive safety sensors are TÜV-certified in accordance with the EU Machinery Directive, Performance Level PLd, Category 2, and SIL2. They are used to safeguard machines and plant components, as well as for reliable position detection in this environment. With their OSSD interface for reliable, redundant shutdown of electronic outputs, they enable easy connection to a safety PLC or fail-safe control interfaces. They can also be operated as standard sensors. The sensors reliably detect standard metal objects in front of the sensor face without coding or similar; there is no blind zone. High characteristic safety values allow longer testing intervals than comparable solutions with a microcontroller. 2 sensors can be connected with 2-channel redundancy and allow PLe as a Category 3 solution.

Dimensions



Technical Data

	2 x normally open (NO)
	PNP
Sn	15 mm
	non-flush
	DC
Sa	0 12.15 mm
	Reference target according EN IEC 60947-5-2 (FE360 - ST37K) 45 mm x 45 mm x 1 mm
	0.5
	0.5

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2023-05-09 Date of issue: 2023-05-09 Filename: 304276-000045_eng.pdf




NSN15-30GM50-2E2-S2D2

Technical Data		
Reduction factor r ₃₀₄		0.8
Reduction factor r _{Brass}		0.55
Output type		4-wire
Nominal ratings		
Operating voltage	U _B	18 30 V
Rated operating voltage	U _e	24 V
Switching frequency	f	0 20 Hz
Hysteresis	Н	typ. 5%
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Overload resistance		yes
Voltage drop	U_d	\leq 3 V at I _L (sum of all outputs) max. 50 mA
Rated insulation voltage	U _{BIS}	30 V
Operating current	IL.	1 30 mA per output
Off-state current	l _r	0 0.5 mA
No-load supply current	I ₀	≤ 15 mA
Time delay before availability	t _v	≤ 300 ms
Switching state indicator		LED, yellow
Error indicator		LED, red
Functional safety related parameters		
Safety Integrity Level (SIL)		SIL 2
Performance level (PL)		PL d
Category		Cat. 2
MTTF _d		> 7500 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		min. 60 %
Assured release distance of a PDDB	S _{ar}	22.5 mm
Compliance with standards and directives		
Standard conformity		
Standards		EN IEC 60947-5-2:2007 EN IEC 60947-5-3:2013 EN ISO 13849-1:2015 EN IEC 61508:2010 EN 62061:2005+AC:2010+A1:2013+A2:2015 compatible with EN ISO 61131-2:2007 Typ 1, 2, 3
Approvals and certificates		
UL approval		cULus Listed, General Purpose, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated \leq 36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Altitude		≤ 2000 m above MSL
Mechanical specifications		
Connection type		cable PVC , 2 m
Core cross section		0.34 mm ²
Housing material		brass, nickel-plated
Sensing face		PBT
Degree of protection		IP68 / IP69
Mass		160 g
General information		-
Scope of delivery		2 self locking nuts in scope of delivery

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Connection



Commissioning

Note for Setting the Safety Control The sensor has a self-monitoring function for the outputs. Therefore, to avoid any malfunctions of the sensor, deactivate all test pulses of the connected safety controller to the sensor.

Acces	sories	
	BF 30	Mounting flange, 30 mm

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3