

Miniature photoelectric slot sensor for the detection of small parts, L design, fork width 5 mm, infrared light, PNP outputs, fixed cable



Function

The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.


Application


- Detection of lead frames
- · Detection of cam positions
- · Detection of limit positions of moving objects
- · Position detection of wafer cases

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Dimensions





Technical Data


General specifications		
Light source		IRED
Light type		Infrared, continuous light, 940 nm
Target size		0.8 x 1.8 mm
Slot width		5 mm
Slot depth		8.5 mm
Ambient light limit		1000 Lux
Functional safety related parameters		
MTTF _d		3760 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Function indicator		red LED lights up when receiving the light beam
Electrical specifications		
Operating voltage	U_B	5 24 V DC , class 2
No-load supply current	I ₀	max. 20 mA
Time delay before availability	t _v	< 2 ms
Output		
Switching type		light/dark on
Signal output		2 PNP complementary, overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 50 mA, resistive load
Voltage drop	U_d	max. 0.2 V at 10 mA max. 0.6 V at 50 mA
Switching frequency	f	max. 5 kHz

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Release date: 2023-05-12 Date of issue: 2023-05-12 Filename: 311658_eng.pdf

Technical Data		
l'oonnoar Bata		
Response time		40 μs Light beam is not interrupted 80 μs Light beam is interrupted
Repeat accuracy	R	0.03 mm
Compliance with standards and directives		
Directive conformity		
EMC Directive 2004/108/EC		EN 60947-5-2:2007+A1:2012
Standard conformity		
Standards		UL 60947-5-2
Approvals and certificates		
UL approval		cULus Recognized, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated \leq 36 V
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-30 80 °C (-22 176 °F)
Pollution degree		2
Mechanical specifications		
Housing width		18.5 mm
Housing height		26 mm
Degree of protection		IP50
Connection		5 m fixed cable
Material		
Housing		PBT
Mass		25 g
Tightening torque, fastening screws		0.6 Nm
Cable length		5 m

Connection Assignment



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".



Response frequency The response frequency is the value when the disc is rotated, see figure.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

