

# Ultrasonic sensor

# UC500-18GS-2EP-IO-V15

- IO-Link Interface for process data, parameterization and diagnosis
- Programmable via DTM with PACTWARE
- Programmable via IrDA (infrared interface)
- Selectable sound lobe width
- Synchronization options
- Enhanced temperature compensation adjustable, stable measuring values already 2 min after switching on
- 2 Push-pull outputs

# Single head system




# **Function**

The UC\*-18GS\*IO\* series ultrasonic sensor combines versatility with a compact housing. All functions can be conviently parameterized via IO-Link or IrDa interface.

A precise interference suppression and the adjustable sound beam width allow an optimal adaptation to your application. The output configuration as well as the sound beam width can also be set directly on the sensor via programming buttons. Process and service data can be transmitted via IO-Link, allowing easy integration into Industry 4.0 applications.

# **Dimensions**



#### **Technical Data**


30 500 mm
50 500 mm
0 30 mm
100 mm x 100 mm
approx. 300 kHz
minimum : 20 ms factory setting: 40 ms
≥ 10 ms (factory setting) ; programmable to 60 s

Temperature influence		with temperature compensation: $\leq \pm 0.75\%$ of the end value 10 min after switching the sensor (factory setting) with enhanced temperature compensation: $\leq \pm 0.75\%$ of the end value 2 min after switching on the sensor without temperature compensation: 0.17 %/K
Memory		
Non-volatile memory		EEPROM
Write cycles		300000
ndicators/operating means		
LED green		solid: power on flashing: standby mode or IO-Link communication
LED yellow		solid: object in evaluation range flashing: switch point programming, object detected
LED red		solid: error flashing: switch point programming, object not detected
Electrical specifications		
Operating voltage	$U_B$	10 30 V DC , ripple 10 % <sub>SS</sub>
No-load supply current	I <sub>0</sub>	≤ 50 mA
Power consumption	$P_0$	≤ 700 mW
Time delay before availability	t <sub>v</sub>	≤ 300 ms
nterface 1		
Interface type		IO-Link (via C/Q = Pin 4)
IO-Link revision		1.1
Device profile		Smart Sensor Profile 2
Process data width		32 bit
Device ID		0x300601 (3147265)
Transfer rate		COM2 (38.4 kBit/s)
Min. cycle time		3 ms
SIO mode support		yes
Compatible master port type		Class A Class B (use 3-pole adapter or 3-wire cable)
nterface 2		
Interface type		IrDA (infrared interface)
Mode		point-to-point connection
Transfer rate		115.2 kBit/s
Maximum communication distance		5 cm
nput/Output		
Input/output type		1 synchronization connection, bidirectional
0 Level		0 1 V
1 Level		2.5 V U <sub>B</sub>
Input impedance		> 22 kΩ
Output rated operating current		current source < 2.5 mA
Pulse length		≥ 1 ms with external control, low active
Synchronization frequency		
Common mode operation		≤ 100 Hz
Multiplex operation		$\leq$ 71 Hz / n , n = number of sensors , n $\leq$ 10
Switching output		
Output type		2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected
Rated operating current	l <sub>e</sub>	100 mA , short-circuit/overload protected
Switching frequency		factory setting: 14 Hz programmable to 33 Hz
Voltage drop		≤ 2.5 V
-		4 . 0 d 0/ . affill apple value
Repeat accuracy		$\leq$ ± 0.1 % of full-scale value
Repeat accuracy Range hysteresis		1 % of the adjusted operating range (default settings), programmable , min. 1 mm



Technical Data	
100mmoar Bata	
Standard conformity	
Standards	EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 IEC 61131-9:2013
Approvals and certificates	
UL approval	cULus Listed, Class 2 Power Source
CCC approval	CCC approval / marking not required for products rated ≤36 V
Ambient conditions	
Ambient temperature	-25 70 °C (-13 158 °F)
Storage temperature	-40 85 °C (-40 185 °F)
Mechanical specifications	
Connection type	Connector plug M12 x 1 , 5-pin
Housing diameter	18 mm
Degree of protection	IP67
Material	
Housing	stainless steel (1.4305 / AISI 303)>BR>PA, PC, POM and PBT plastic parts
Transducer	epoxy resin/hollow glass sphere mixture; polyurethane foam
Installation position	any position
Mass	45 g
Tightening torque, fastening screws	max. 30 Nm
Factory settings	
Output 1	near switch point: 50 mm far switch point: 500 mm output function: Window mode output behavior: NO contact
Output 2	near switch point: 50 mm far switch point: 250 mm output function: Window mode output behavior: NO contact
Beam width	wide

# Connection



# **Connection Assignment**




Wire colors in accordance with EN 60947-5-2

1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)
5 GY (gray)


# **Characteristic Curve**


# Characteristic response curve




### Switching output modes

1. Switch point mode






3. Hysteresis mode



4. Retroreflective mode



# **Accessories**



**UC-PROG-IR-USB** 

Interface cable for parameterization of sensors with IrDA interface



V1-G-2M-PVC-V1-G

Cordset M12 socket straight to M12 plug straight A-coded, 4-pin, PVC cable grey

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Release date: 2022-12-13 Date of issue: 2022-12-13 Filename: 304928-100000\_eng.pdf

# Accessories **BF 18** Mounting flange, 18 mm BF 18-F Plastic mounting adapter, 18 mm **AB-18** Mounting aid **OMH-04** Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm BF 5-30 Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm UVW90-K18 Ultrasonic -deflector V15-G-2M-PVC Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey V15-W-2M-PUR Female cordset single-ended M12 angled A-coded, 5-pin, PUR cable grey ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors

# **Function**

#### Adjustment possibilities

The sensor features 2 switching outputs with each 2 programmable switch points. Programming the switch points, the output mode, the output logic and the beam width can be done in two different ways:

- · Using the sensor's programming buttons
- Using the IO-link interface of the sensor. This method requires an IO-link master (e.g. IO-link-Master02-USB) and the associated software.
   The download link is available on the product page for the sensor at www.pepperl-fuchs.

#### **Synchronization**

The sensor features a synchronization input for suppressing ultrasonic mutual interference ("cross talk").

The following synchronization modes are available:

- 1. Automatic multiplex mode.
- 2. Automatic common mode
- 3. Externally controlled synchronization

#### **Further Documentation**

- For information on programming via programming buttons and synchronisation you may refer to the commissioning instruction.
- For detailed information on application and programming via IO-Link we provide a manual.