

NRB8-18GM40-E2-IO-C



- Reduction factor = 1
- Magnetic field resistant
- Weld Immune
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set




Function

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

Dimensions




Technical Data

General specifications		
Switching function		Normally open/closed (NO/NC) programmable
Output type		PNP
Rated operating distance	Sn	8 mm (factory setting)
Near operating distance		5 mm (can be activated by software)
Installation		flush
Output polarity		DC
Assured operating distance	Sa	0 6.48 mm
Reduction factor r _{Al}		1
Reduction factor r _{Cu}		1

Technical Data		
Reduction factor r ₃₀₄		1
Reduction factor r _{St37}		1
Output type		3-wire
Nominal ratings		
Operating voltage	U _B	10 30 V DC
Switching frequency	f	0 1500 Hz (switch point mode) 0 150 Hz (window mode, switch point mode with stability alarm)
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_d	≤ 0.5 V
Operating current	IL	0 200 mA
Off-state current	l _r	0 0.5 mA typ. 60 μA at 25 °C
No-load supply current	I _o	≤ 15 mA
Time delay before availability	t _v	max. 150 ms
Constant magnetic field	В	200 mT
Alternating magnetic field	В	200 mT
Status indicator		LED yellow
Functional safety related parameters		,
MTTF _d		362 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0%
Interface		
Interface type		IO-Link (via C/Q)
IO-Link revision		1.1
Device ID		0x201112 (2101522)
Transfer rate		COM2 (38.4 kBaud)
Min. cycle time		2.3 ms
Process data width		Process data input (control system side): 2 Bit
SIO mode support		Process data output (control system side): none yes
Compatible master port type		A
Compliance with standards and directives		n
Standard conformity		
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007
Approvale and scutificates		IEC 60947-5-2 AMD 1:2012
Approvals and certificates		
Protection class		
Rated insulation voltage	Ui	60 V
Rated impulse withstand voltage UL approval	U _{imp}	800 V cULus Listed, General Purpose
CCC approval		Class 2 power source CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		cable PUR , 2 m
Cornection type Core cross section		0.34 mm ²
Housing material		Brass, PTFE coated PPS
Sensing face		
Degree of protection Cable		IP67

Connection




Function Principle

Switching output modes

Switch point mode at rated operating distance s_n

Switch point 2 SP 2 (rated operating distance s_n)




Switch point mode with near operating distance

Switch point 1 SP1 (near operating distance) Normally open Normally closed


Window mode

Switch point 2 SP 2 (rated operating distance s_{n}) Switch point 1 SP1 (near operating distance)




Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance s_n)



Accessories

	BF 18	Mounting flange, 18 mm
ll-o	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs
le le	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs
9	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
	ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals
8	ICE3-8IOL-K45S-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
S. C.	IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection
	ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs
000	ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs
	ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors