

Inductive sensor

NRN30-30GM50-E2-IO-C-V1

- 30 mm non-flush
- Reduction factor = 1
- Magnetic field resistant
- Weld Immune
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set




Function

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

Dimensions



Technical Data


General specifications				
Switching function		Normally open/closed (NO/NC) programmable		
Output type		PNP		
Rated operating distance	s_n	30 mm (factory setting)		
Near operating distance		20 mm (can be activated by software)		
Installation		non-flush		
Output polarity		DC		

Sa	0 24.3 mm
	1
	1
	1
	1
	3-wire
U₀	10 30 V DC
f	680 Hz (switch point mode) 50 Hz (window mode, switch point mode with stability alarm)
Н	typ. 3 %
	reverse polarity protected
	pulsing
U_d	≤ 0.5 V
IL.	0 200 mA
I _r	0 0.5 mA typ. 60 μA at 25 °C
I ₀	≤ 15 mA
	max. 150 ms
	200 mT
	200 mT
_	Multihole-LED, yellow
	360 a
	20 a
	0%
	0 /0
	IO-Link (via C/Q = pin 4)
	1.1
	0x201116 (2101526) COM2 (38.4 kBit/s)
	2.3 ms
	Process data input (control system side): 2 Bit
	Process data output (control system side): none
	yes
	A
	EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
	II
U_{i}	60 V
U_{imp}	800 V
	cULus Listed, General Purpose Class 2 power source
	CCC approval / marking not required for products rated ≤36 V
	ood approvary marking not required for products rated 300 v
	ooo approvar/ marking not required for products rated 200 v
	-25 70 °C (-13 158 °F)
	-25 70 °C (-13 158 °F)
	-25 70 °C (-13 158 °F)
	-25 70 °C (-13 158 °F) -40 85 °C (-40 185 °F)
	U _d I _L I _r I ₀ t _v B B



Technical Data		
Degree of protection	IP67	
Mass	137 g	
Factory settings		
Default setting	operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 30 mm	
General information		
Scope of delivery	2 self locking nuts in scope of delivery	

Connection



Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Switching output modes


Switch point mode at rated operating distance $\boldsymbol{s}_{\boldsymbol{n}}$

Switch point 2 SP 2 (rated operating distance s_{n)}




Switch point mode with near operating distance

Switch point 1 SP1 (near operating distance)



Window mode

Switch point 2 SP 2 (rated operating distance $\boldsymbol{s}_{n)}$




Stability alarm

Switch point mode with stability alarm (factory default)

Switch point 2 SP 2 (rated operating distance $s_{n)}$ Normally Normally closed LED

Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance s_n)



Accessories

BF 30	Mounting flange, 30 mm
V1-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey

Accessories V1-W-2M-PUR Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors Female cordset single-ended M12 straight A-coded, 4-pin, POC cable welding-bead resistant orange, V1-G-OR2M-POC suitable for robotic applications, torsion resistant, oil resistant, molecularly cross-linked