

Inductive sensor

NRN30-30GM50-E2-IO-C

- 30 mm non-flush
- Reduction factor = 1
- Magnetic field resistant
- Weld Immune
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set




Function

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.


Dimensions



Technical Data


General specifications				
Switching function		Normally open/closed (NO/NC) programmable		
Output type		PNP		
Rated operating distance	Sn	30 mm (factory setting)		
Near operating distance		20 mm (can be activated by software)		
Installation		non-flush		
Output polarity		DC		
Assured operating distance	Sa	0 24.3 mm		
Reduction factor r _{Al}		1		
Reduction factor r _{Cu}		1		

Reduction factor r ₃₀₄		1
Reduction factor r _{St37}		1
Output type		3-wire
lominal ratings		
Operating voltage	U _B	10 30 V DC
Switching frequency	f	0 680 Hz (switch point mode) 0 50 Hz (window mode, switch point mode with stability alarm)
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_d	≤ 0.5 V
Operating current	IL	0 200 mA
Off-state current	I_r	$0 \dots 0.5$ mA typ. $60~\mu\text{A}$ at $25~^{\circ}\text{C}$
No-load supply current	Io	≤ 15 mA
Time delay before availability	t_{v}	max. 150 ms
Constant magnetic field	В	200 mT
Alternating magnetic field	В	200 mT
Status indicator		LED yellow
unctional safety related parameters		
MTTF _d		360 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
nterface		
Interface type		IO-Link (via C/Q)
IO-Link revision		1.1
Device ID		0x201116 (2101526)
Transfer rate		COM2 (38.4 kBit/s)
Min. cycle time		2.3 ms
Process data width		Process data input (control system side): 2 Bit Process data output (control system side): none
SIO mode support		yes
Compatible master port type		A
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
Approvals and certificates		
Protection class		II
Rated insulation voltage	Ui	60 V
Rated impulse withstand voltage	U _{imp}	800 V
UL approval	шр	cULus Listed, General Purpose Class 2 power source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
lechanical specifications		
Connection type		cable PUR , 2 m
Core cross section		0.34 mm ²
Housing material		Brass, PTFE coated
Sensing face		PPS
Degree of protection		IP67
Cable		



$4.3 \text{ mm} \pm 0.1 \text{ mm}$
> 10 x cable diameter
170 g
operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 30 mm
2 self locking nuts in scope of delivery

Connection



Function Principle

Switching output modes


Switch point mode at rated operating distance $\mathbf{s}_{\mathbf{n}}$

Switch point 2 SP 2 (rated operating distance s_{n})



Switch point mode with near operating distance

Switch point 1 SP1 (near operating distance) Normally open




Window mode

Switch point 2 SP 2 (rated operating distance $s_{n)}$ Switch point 1 SP1 (near operating distance) Normally open Normally closed

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"


Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance $s_{n)}$



Accessories

	BF 30	Mounting flange, 30 mm
II-	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs
11	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs
	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
	ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals
9	ICE3-8IOL-K45S-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
S. I.	IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection
	ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs
0 : 0 0 : 0 0 : 0 0 : 0 1 : 0 0 : 0	ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs
	ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors