

Inductive sensor NRB8-18GS40-E2-IO


- 8 mm flush
- Reduction factor = 1
- Magnetic field resistant
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set

Function

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

Dimensions



_		
Гес		

	Normally open/closed (NO/NC) programmable
	PNP
Sn	8 mm (factory setting)
	5 mm (can be activated by software)
	flush
	DC
Sa	0 6.48 mm
	1
	1

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com



NRB8-18GS40-E2-IO

Technical Data		
Reduction factor r ₃₀₄		1
Reduction factor r _{St37}		1
Output type		3-wire
Nominal ratings		
Operating voltage	UB	10 30 V DC
Switching frequency	f	0 1500 Hz (switch point mode) 0 150 Hz (window mode, switch point mode with stability alarm)
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_{d}	≤ 0.5 V
Operating current	IL.	0 200 mA
Off-state current	l _r	0 0.5 mA typ. 60 μA at 25 °C
No-load supply current	I ₀	≤ 15 mA
Time delay before availability	t _v	max. 150 ms
Constant magnetic field	В	200 mT
Alternating magnetic field	В	200 mT
Status indicator		LED yellow
Functional safety related parameters		•
MTTFd		362 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
nterface		
Interface type		IO-Link (via C/Q)
IO-Link revision		1.1
Device ID		0x201102 (2101506)
Transfer rate		COM2 (38.4 kBit/s)
Min. cycle time		2.3 ms
Process data width		Process data input (control system side): 2 Bit Process data output (control system side): none
SIO mode support		yes
Compatible master port type		A
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
Approvals and certificates		
Protection class		I
Rated insulation voltage	Ui	60 V
Rated impulse withstand voltage	U _{imp}	800 V
UL approval	μų	cULus Listed, General Purpose Class 2 power source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		cable PVC , 2 m
Core cross section		0.34 mm ²
Housing material		Stainless steel 1.4305 / AISI 303
Housing material Sensing face		Stainless steel 1.4305 / AISI 303 PBT
Housing material Sensing face Degree of protection		


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

NRB8-18GS40-E2-IO

Technical Data

Cable diameter	4.3 mm ± 0.1 mm
Bending radius	> 15 x cable diameter
Mass	101 g
Factory settings	
Default setting	operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 8 mm
General information	
Scope of delivery	2 self locking nuts in scope of delivery

Connection



Function Principle

Switching output modes

Switch point mode at rated operating distance $\mathbf{s}_{\mathbf{n}}$


Switch point 2 SP 2 (rated operating distance $s_{n)}$



Switch point mode with near operating distance

Switch point 1 SP1 (near operating distance)
Normally
Normally
Closed

Window mode



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"


3

Function Principle

NRB8-18GS40-E2-IO


Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance s_n)



Accessories

BF 18	Mounting flange, 18 mm
ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs
 ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs
ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals
ICE3-8IOL-K45S-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection
ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs
ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs
ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

