

# Inductive sensor

## NRN30-30GS50-E2-IO-V1

- 30 mm non-flush
- Reduction factor = 1
- Magnetic field resistant
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set




### **Function**

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

### **Dimensions**



## **Technical Data**

Release date: 2022-06-30 Date of issue: 2022-06-30 Filename: 306533-0023\_eng.pdf

General specifications		
Switching function		Normally open/closed (NO/NC) programmable
Output type		PNP
Rated operating distance	$s_n$	30 mm (factory setting)
Near operating distance		20 mm (can be activated by software)
Installation		non-flush
Output polarity		DC

Pepperl+Fuchs Group


www.pepperl-fuchs.com

Technical Data

#### Assured operating distance 0 ... 24.3 mm Reduction factor rAI Reduction factor r<sub>Cu</sub> 1 Reduction factor r<sub>304</sub> 1 Reduction factor r<sub>St37</sub> Output type 3-wire **Nominal ratings** Operating voltage $U_B$ 10 ... 30 V DC 0 ... 680 Hz (switch point mode) 0 ... 50 Hz (window mode, switch point mode with stability alarm) Switching frequency typ. 3 % Hysteresis Reverse polarity protection reverse polarity protected Short-circuit protection pulsing ≤ 0.5 V Voltage drop $U_{d}$ Operating current $I_{\mathsf{L}}$ 0 ... 200 mA Off-state current 0 ... 0.5 mA typ. 60 μA at 25 °C No-load supply current $I_0$ ≤ 15 mA Time delay before availability max. 150 ms $t_{v}$ Constant magnetic field В 200 mT 200 mT R Alternating magnetic field Multihole-LED, yellow Status indicator Functional safety related parameters 360 a $MTTF_d$ 20 a Mission Time (T<sub>M</sub>) 0 % Diagnostic Coverage (DC) Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision 1.1 Device ID 0x201106 (2101510) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms Process data input (control system side): 2 Bit Process data output (control system side): none Process data width SIO mode support yes Compatible master port type Α Compliance with standards and directives Standard conformity Standards EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012 Approvals and certificates Protection class Ш 60 V Rated insulation voltage $U_i$ Rated impulse withstand voltage $U_{\text{imp}}$ 800 V **UL** approval cULus Listed, General Purpose Class 2 power source CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -25 ... 70 °C (-13 ... 158 °F) Ambient temperature Storage temperature -40 ... 85 °C (-40 ... 185 °F) Mechanical specifications Connection type Connector plug M12 x 1, 4-pin Housing material Stainless steel 1.4305 / AISI 303 PBT Sensing face

Technical Data		
Degree of protection	IP67	
Mass	137 g	
Factory settings		
Default setting	operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 30 mm	
General information		
Scope of delivery	2 self locking nuts in scope of delivery	

## **Connection**



# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2

1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)


# Switching output modes

### Switch point mode at rated operating distance $\boldsymbol{s}_{\boldsymbol{n}}$

Switch point 2 SP 2 (rated operating distance s<sub>n)</sub>



### Switch point mode with near operating distance



#### Window mode


Switch point 2 SP 2 (rated operating distance s<sub>n</sub>)

Switch point 1 SP1 (near operating distance)

Normally open

### Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance s<sub>n</sub>)

Switch point 1 SP1 (near operating distance)

Normally open

Normally closed

## **Accessories**

BF 30	Mounting flange, 30 mm
V1-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey

**Accessories** 

# V1-W-2M-PVC Female cordset, M12, 4-pin, PVC cable ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors