

## Inductive sensor NRN40-L3K-E2-IO-C-V1

- 40 mm non-flush
- Reduction factor = 1
- Magnetic field resistant
- Weld Immune
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set
- 4-way LED indicator
- Quick mounting bracket


# 


#### **Function**


Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

## Dimensions







## **Technical Data**

#### **General specifications**

#### Switching function

Output type

Switching function

Normally open/closed (NO/NC) programmable PNP

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"




Technical Data		
Rated operating distance	Sn	40 mm (factory setting)
Near operating distance	-11	35 mm (can be activated by software)
Installation		non-flush
Output polarity		DC
Assured operating distance	Sa	0 32.4 mm
Reduction factor r <sub>Al</sub>	a	1
Reduction factor r <sub>Cu</sub>		1
Reduction factor r <sub>304</sub>		1
Reduction factor r <sub>St37</sub>		1
Output type		3-wire
Nominal ratings		
Operating voltage	U <sub>B</sub>	10 30 V DC
Switching frequency	f	0 180 Hz (switch point mode) 0 30 Hz (window mode, switch point mode with stability alarm)
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	$U_d$	≤ 0.5 V
Operating current	ΙL	0 200 mA
Off-state current	l <sub>r</sub>	0 0.5 mA typ. 60 μA at 25 °C
No-load supply current	I <sub>0</sub>	≤ 20 mA
Time delay before availability	t <sub>v</sub>	max. 150 ms
Constant magnetic field	В	200 mT
Alternating magnetic field	В	200 mT
Operating voltage indicator		LED, green
Status indicator		LED, yellow
Functional safety related parameters		
MTTF <sub>d</sub>		701 a
Mission Time $(T_M)$		20 a
Diagnostic Coverage (DC)		0 %
Interface		
Interface type		IO-Link (via $C/Q = pin 4$ )
IO-Link revision		1.1
Device ID		0x201004 (2101252)
Transfer rate		COM2 (38.4 kBit/s)
Min. cycle time		2.3 ms
Process data width		Process data input (control system side): 2 Bit Process data output (control system side): none
SIO mode support		yes
Compatible master port type		A
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
Approvals and certificates		
Protection class	11	II 60 V
Rated insulation voltage	U <sub>i</sub>	800 V
Rated impulse withstand voltage	U <sub>imp</sub>	cULus Listed, General Purpose
UL approval CCC approval		COLus Listed, General Purpose Class 2 power source CCC approval / marking not required for products rated ≤36 V
Ambient conditions		ooo approvar / marking not required for products rated 500 v
Ambient conditions Ambient temperature		-25 70 °C (-13 158 °F)
		-20 70° O (-10 100° F)

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## NRN40-L3K-E2-IO-C-V1

Technical Data	
Storage temperature	-40 85 °C (-40 185 °F)
Mechanical specifications	
Connection type	Connector plug M12 x 1 , 4-pin
Housing material	GD-ZnAl4Cu1, coated mounting flange PA6-GF35
Sensing face	PA 6 Grivory GVN-35H
Degree of protection	IP67
Mass	190 g
Factory settings	
Default setting	operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 40 mm

### Connection



## **Connection Assignment**



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

3

## **Function Principle**


#### Switching output modes

#### Switch point mode at rated operating distance $\mathbf{s}_{\mathbf{n}}$

Switch point 2 SP 2 (rated operating distance  $s_{n}$ )




#### Switch point mode with near operating distance




#### Window mode

Switch point 2 SP 2 (rated operating distance  $s_{n)}$ 




#### Stability alarm

Switch point mode with stability alarm (factory default)



#### Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance sn)



## Accessories

ø /	V1-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey
6/	V1-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

4

## NRN40-L3K-E2-IO-C-V1

Δ	CC	AC	 rı	es
<u></u>		60		60

	001100	
	MHW 01	Modular mounting bracket
	MH 02-L	Mounting aid for VariKont-L
	MH 04-2681F	Mounting aid for VariKont, +U1+ and +U9*
In	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs
and the second	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs
	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
	ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals
	ICE3-8IOL-K45S-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal
	IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection
	ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs
	ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs
	ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors
ø /	V1-G-OR2M-POC	Female cordset single-ended M12 straight A-coded, 4-pin, POC cable welding-bead resistant orange, suitable for robotic applications, torsion resistant, oil resistant, molecularly cross-linked

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

5