

## Inductive sensor

## NRN40-U1-E2-IO-V1

- 40 mm non-flush
- Reduction factor = 1
- Magnetic field resistant
- IO-Link interface for service and process data
- Switch point mode or window mode can be set
- Switching function, stability alarm and pulse extension can be set
- 4-way LED indicator
- Quick mounting bracket




### **Function**

Reduction factor 1 sensors reliably detect different metals with the same switch state.

The integrated IO-Link interface enables clear identification of the sensor and diagnosis of the sensor condition. When using the sensor, parameters and operating modes can be optimally configured specifically for the intended application. In addition to setting the switching function and a pulse extension, the user can select either switch point mode or window mode in combination with a stability alarm. In switch point mode, the stability alarm signals the detection of an object in the area between the assured operating distance and operating distance sn. In window mode, it signals the detection of an object below the window between operating distance sn and the nearest operating distance. A stability alarm is displayed to the user via a flashing LED and process data.

### **Dimensions**



### **Technical Data**

General specifications	
Switching function	Normally open/closed (NO/NC) programmable
Output type	PNP



#### Technical Data Rated operating distance 40 mm (factory setting) 35 mm (can be activated by software) Near operating distance Installation non-flush DC Output polarity Assured operating distance 0 ... 32.4 mm Sa Reduction factor r<sub>AI</sub> Reduction factor r<sub>Cu</sub> 1 Reduction factor r<sub>304</sub> 1 Reduction factor r<sub>St37</sub> Output type 3-wire **Nominal ratings** Operating voltage $U_{\mathsf{B}}$ 10 ... 30 V DC Switching frequency 0 ... 180 Hz (switch point mode) 0 ... 30 Hz (window mode, switch point mode with stability alarm) Hysteresis Н tvp. 3 % Reverse polarity protection reverse polarity protected Short-circuit protection pulsing Voltage drop $U_{\text{d}}$ ≤ 0.5 V Operating current $I_{L}$ 0 ... 200 mA 0 ... 0.5 mA typ. 60 μA at 25 °C Off-state current No-load supply current $I_0$ ≤ 20 mA Time delay before availability max. 150 ms $t_v$ Constant magnetic field В 200 mT В 200 mT Alternating magnetic field Operating voltage indicator LED, green Status indicator LED, yellow Functional safety related parameters $\mathsf{MTTF}_\mathsf{d}$ 701 a Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) 0 % Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision 1.1 Device ID 0x201006 (2101254) COM2 (38.4 kBit/s) Transfer rate Min. cycle time 2.3 ms Process data input (control system side): 2 Bit Process data width Process data output (control system side): none SIO mode support yes

Compliance with standards and directives Standard conformity

EN 60947-5-2:2007 EN 60947-5-2/A1:2012 Standards

IEC 60947-5-2:2007

Α

IEC 60947-5-2 AMD 1:2012

Approvals and certificates

Compatible master port type

Protection class		II
Rated insulation voltage	Ui	60 V
Rated impulse withstand voltage	$U_{\text{imp}}$	800 V

cULus Listed, General Purpose **UL** approval Class 2 power source

CCC approval CCC approval / marking not required for products rated ≤36 V


**Ambient conditions** 

-25 ... 70 °C (-13 ... 158 °F) Ambient temperature



Technical Data	
Storage temperature	-40 85 °C (-40 185 °F)
Mechanical specifications	
Connection type	Connector plug M12 x 1 , 4-pin
Housing material	PA/metal with epoxy powder coating
Sensing face	PA 6 Grivory GVN-35H
Housing base	plastic
Degree of protection	IP67
Mass	280 g
Note	Tightening torque: 1.8 Nm (housing)
Factory settings	
Default setting	operating mode = switch point mode with stability alarm switching function = Normally open (NO) switching distance = 40 mm

## Connection



# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	RK	(black)

Inductive sensor NRN40-U1-E2-IO-V1

### **Function Principle**


#### Switching output modes

### Switch point mode at rated operating distance $\boldsymbol{s}_{\boldsymbol{n}}$

Switch point 2 SP 2 (rated operating distance s<sub>n)</sub>



#### Switch point mode with near operating distance



#### Window mode


Switch point 2 SP 2 (rated operating distance s<sub>n</sub>)

Switch point 1 SP1 (near operating distance)

Normally open


### Stability alarm

Switch point mode with stability alarm (factory default)



Window mode with stability alarm

Switch point 2 SP 2 (rated operating distance  $s_{n}$ )



### **Accessories**

V1-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey
V1-W-2M-PVC	Female cordset, M12, 4-pin, PVC cable

# **Accessories MHW 01** Modular mounting bracket MH 02-L Mounting aid for VariKont-L MH 04-2681F Mounting aid for VariKont, +U1+ and +U9\* ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G30L-V1D ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors

