



Retroreflective sensor ML100-54-F/25/102/115/154



- Miniature design
- No controls
- Easy to use
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- Very bright, highly visible light spot
- Full metal thread mounting
- Not sensitive to ambient light
- Optimized for small distances to any reflector
- Mounting optical reflective films down to a distance of 20 mm

Retroreflective sensor with polarization filter, plastic housing, 3 m detection range, red light, light on, DC version, NPN output, fixed cable








Function

The optical sensors of this series are suitable for both standard and demanding applications.

The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions




		1		
-	nn			ta
ᆫ		ıcal		


General specifications		
Effective detection range		0 2.7 m
Reflector distance		0.02 2.7 m (0.02 1 m on OFR-100/100 optical reflective film)
Threshold detection range		3 m
Reference target		H50 reflector
Light source		LED
Light type		modulated visible red light
Polarization filter		yes
Diameter of the light spot		approx. 200 mm at a distance of 3 m
Opening angle		approx. 4 °
Optical face		frontal
Ambient light limit		EN 60947-5-2:2007+A1:2012
Functional safety related parameters		
MTTF _d		860 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Operation indicator		LED green: power on
Function indicator		LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted
Electrical specifications		
Operating voltage	U _B	10 30 V DC

Technical Data		
Ripple		max. 10 %
No-load supply current	I ₀	< 20 mA
Output		
Switching type		light-on
Signal output		1 NPN output, short-circuit protected, reverse polarity protected, open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA, resistive load
Voltage drop	U _d	≤ 1.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-30 60 °C (-22 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		11 mm
Housing height		31 mm
Housing depth		20 mm
Degree of protection		IP67
Connection		2 m fixed cable
Material		
Housing		PC (Polycarbonate)
Optical face		PMMA
Mass		approx. 50 g
Tightening torque, fastening screws		0.6 Nm
Cable length		2 m

Connection





Indication



1	Signal display	vellow	
2	Operating display	green	

Characteristic Curve





Accessories

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
*	OMH-F10-ML100	Mounting aid for ML100 series
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket

1	<u>+</u>
	C
	Ċ
	_
	C
	Ċ
	≂
	u
п	c
ı	Ξ.
	3
- 3	a
п	`
-	_
	×
•	٠.
	٠.
	a
	7
	ၽ
	₹
	ä
	÷
	α
:	
ı	1
-	_
-	c
-	_
	٠.
	ċ
•	÷
	۵
(т.
- (1
i	-
ò	≍
,	٠,
	à
	₫
	٠ <u>۱</u>
	<u>a</u>
	٠ ١
:	
;	- di 000
	01000
;	0 0 0 0
	ים וממו דם מו
	ישו היים דרי
:	Date of Ign Ip.
:) ate of 1881 le
	Date Of ISSUE
	ישומטולים בעלו ל
	ים ואטן לר
	- 15 Date Of 150 Ip.
	6-15 Date Of ISSUE.
	- 15 Date Of 155 ID
	-01-12 Date Of 1881 P
	4-15-15 Date Of ISSUE
	-3-()-12 Date (1-12)
	7.3-10-12 Date Of 18816
	0.23-06-15 Date of ISS ID
	7.7.4.05-15-15-15-15-15-15-15-15-15-15-15-15-15
	- 2.2.3.10 Jate Of 18816
	9. 27.2-(12-12-12-12-12-12-12-12-12-12-12-12-12-1
	To. 2723-(16-15) 216 Of 18816
	212. 212.3-10-12 Date Of ISSUE
	27.7.3-12-12-12-12-12-12-12-12-12-12-12-12-12-
	Cate. 2723-12-12 Jate of 1881 P.
	2 Cate 7 7 7 4 (12 - 12) ate Ct 1881 6
	30 Cate. 2024-06-15 Jate of 18816.
	Se date: 2023-05-15 Date of ISSUE.
	2003-10-12 Jate Of Issue.
	שמעם כמונט אינוייט - יטנייט מונט מונט מונט מונט מונט מונט מונט מונ
	מושמים כמום כן כנייטיין אינייטין מעום כן ומצוום.
	Jales Cate 7073-06-15 Date Of Isolie

Accessories			
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket	
	OMH-10	Mounting aid for ML100 series	
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole	
	REF-H60-2	Reflector with mounting holes	
	REF-H33	Reflector with screw fixing	
	OFR-70-2	Reflective tape 70 mm x 70 mm	
61	V31-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey	
6/	V31-GM-2M-PUR	Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey	
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes	
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap	
	OFR-100/100	Reflective tape 100 mm x 100 mm	