

RFID read/write device IUH-F190-V1-FR2-12

- Flexible UHF read/write device with medium detection range
- Ready-made PLC function blocks designed for quick and easy system integration
- Compact and robust housing for harsh industrial environments
- Switchable antenna polarization guarantees reliable tag detection and enhances process flow
- For connection to IDENTControl control interface
- Multi-tag reading increases productivity

UHF RFID read/write device for IDENTControl, Thailand and Hong Kong

Function

The compact IUH-F190-V1-FR2-12 read/write head operates in the UHF frequency range and is optimized for use in industrial applications involving medium distances. The device reads and writes passive tags in line with EPC Generation 2 (ISO/IEC 18000-63). The read/write head can be used in Thailand and Hong Kong. The read/write head is compliant with the relevant transmiśsion regulations.

Wide range of options supported for filtering data.

The read/write head is connected to the IDENTControl interface using an M12 connector.

The user can monitor the status of the read/write head using the integrated LEDs. The read/write head has a typical detection range of around 2 meters; this range is determined by the tag used and can be adjusted by configuring the transmission power.

Other influencing factors include the setup and installation of the specific application and the surrounding materials, particularly metal. The read and write distances for the relevant tag, which are detailed separately, have been established in a test laboratory under ideal conditions. For the actual read and write distances under real conditions, the combination of read/write head and tag must be tested in the desired application.

Application


This product is a wireless device and may be operated only in the country for which a transmission license exists. Information regarding transmission licenses can be found on the datasheet for the product. If a product is released to a customer in a country for which there is no

transmission license, the product may be operated only in the country for which a transmission license exists.

If a product does not correspond to the legal requirements in force in the EU but is released to a purchaser within the EU, the product is intended for use solely in the destination country of the end customer outside of the EU for which a transmission license exists. The product may therefore under no circumstances be used directly by the purchaser or released to third parties for the purpose of distribution, application or use on the market within the EU as part of a commercial activity.

In the event of an infringement, the purchaser is obliged to indemnify the supplier against any resulting damages, costs, penalty payments and other expenses.

Dimensions






| ₽ |
|--------------------------------------------------|
| φ |
| 5_eng |
| 5 |
| 8 |
| 309845 |
| a E |
| ena |
| ≝ |
| 4 |
| 8 |
| 9 |
| 202 |
| <u>e</u> |
| ssn |
| 5 |
| ate |
| Õ |
| Š |
| ĕ |
| 2023-08-04 Date of issue: 2023-08-04 Filename: (|
| χ |
| se date: 2 |
| se d |

| General specifications | | |
|----------------------------|-------|---------------------------------------------------------------------------------------------------------------------------------|
| Operating frequency | | 920 MHz 925 MHz: Thailand, Hong Kong |
| | | Transmission licenses for other countries on request |
| Emitted power | | 3 1250 mW EIRP adjustable |
| Operating distance | | typ. 2 m |
| MTBF | | 105 a (Operation at +40 °C) |
| Indicators/operating means | | |
| LED green | | Power on |
| LED yellow | | Read/write operation successful |
| LED blue | | Transmission mode |
| Electrical specifications | | |
| Current consumption | | ≤ 450 mA |
| Power consumption | P_0 | ≤9 W |
| Supply | | from the IDENTControl |
| Surge protection | | category 2 |
| Standard conformity | | |
| Degree of protection | | EN 60529 |
| RFID | | ISO/IEC 18000-63 |
| Ambient conditions | | |
| Classification | | Environmental condition A (controlled environment) |
| Ambient temperature | | -20 70 °C (-4 158 °F) (Operation with nontransmission periods, adjustable) -20 60 °C (-4 140 °F) (Continuous transmission mode) |
| Storage temperature | | -40 85 °C (-40 185 °F) |
| Pollution degree | | 2 |
| Mechanical specifications | | |
| Housing length | | 114 mm |
| Housing width | | 112 mm |
| Housing height | | 63 mm |
| Degree of protection | | IP67 |
| Connection | | connector M12 x 1 |
| Material | | |
| Housing | | PA 6.6 |
| Base | | diecast aluminum |
| Mass | | 860 g |
| | | |

Connection






+ A -B do not connect

Shield

Accessories





Accessories IC-KP2-2HB6-V15B Control interface unit IDENTControl Compact with interface for PROFIBUS DP IC-KP2-2HB17-2V1D IDENTControl Compact control interface with Ethernet interface for TCP/IP, PROFINET, EtherNet/IP, and MODBUS TCP protocols IC-KP2-2HB21-2V1D Control interface unit IDENTControl Compact with EtherCAT interface IUC76-F157-T19-M-FR2 Data carrier for autoclave applications IUC77-25L100-GBL Data carrier 1000pcs IUC77-28L90-M-FR2 Data carrier 25pcs IUC77-34-M-FR2 10pcs Data carrier IUC77-50-FR2 10pcs Data carrier IUZ-MH13 Mounting bracket for wall mounting IUZ-MH15 Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm V1-G-2M-PUR-ABG-V1-W Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded V1-G-5M-PUR-ABG-V1-W Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded V1-G-10M-PUR-ABG-V1-W Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded