

# **RFID** read/write device IUH-F190-V1-FR1-15

- Flexible UHF read/write device with medium detection range
- Ready-made PLC function blocks designed for quick and easy system integration
- Compact and robust housing for harsh industrial environments
- Switchable antenna polarization guarantees reliable tag detection and enhances process flow
- For connection to IDENTControl control interface
- Multi-tag reading increases productivity

UHF RFID read/write device for IDENTControl, Morocco




### Function

The read/write head operates in the UHF frequency range and is optimized for use in industrial applications involving medium distances. The device reads and writes passive tags acc. to EPC Generation 2 (ISO/IEC 18000-63). The read/write head is compliant with the relevant transmission regulations.

The read/write head can be used in Morocco.

The read/write head can be used in Morocco. Wide range of options supported for filtering data. The read/write head is connected to the IDENTControl interface using an M12 connector. The user can monitor the status of the read/write head using the integrated LEDs. The read/write head has a typical detection range of around 2 meters; this range is determined by the tag used and can be adjusted by configuring the transmission power. Other influencing factors include the setup and installation of the specific application and the surrounding materials, particularly metal. The read and write distances for the relevant tag, which are detailed separately, have been established in a test laboratory under ideal conditions. For the actual read and write distances under real conditions, the combination of read/write head and tag must be tested in the desired application.

## Dimensions



# **Technical Data**

#### **General specifications** Operating frequency 867.6 ... 868 MHz: Morocco Transmission licenses for other countries on request Emitted power 3 ... 500 mW ERP adjustable Operating distance typ. 2 m MTBF 105 a (Operation at +40 °C) Indicators/operating means LED green Power on

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com




### **Technical Data**

### IUH-F190-V1-FR1-15

LED yellow		Read/write operation successful
LED blue		Transmission mode
Electrical specifications		
Current consumption		≤ 450 mA
Power consumption	P <sub>0</sub>	≤9W
Supply		from the IDENTControl
Surge protection		category 2
Standard conformity		
Degree of protection		EN 60529
RFID		ISO/IEC 18000-63
Ambient conditions		
Classification		Environmental condition A (controlled environment)
Ambient temperature		-20 70 °C (-4 158 °F) (Operation with nontransmission periods, adjustable) -20 60 °C (-4 140 °F) (Continuous transmission mode)
Storage temperature		-40 85 °C (-40 185 °F)
Pollution degree		2
Mechanical specifications		
Housing length		114 mm
Housing width		112 mm
Housing height		63 mm
Degree of protection		IP67
Connection		connector M12 x 1
Material		
Housing		PA 6.6
Base		diecast aluminum
Mass		810 g

# Connection







+

Acces	sories	
Contraction of the second	IC-KP-B17-AIDA1	IDENTControl control interface with Ethernet interface for TCP/IP, PROFINET, EtherNet/IP, and MODBUS TCP protocols
( <b>1</b> )	IC-KP2-2HRX-2V1	Control interface unit IDENTControl Compactwith serial interface RS-232 and RS-485
	IC-KP2-2HB6-V15B	Control interface unit IDENTControl Compact with interface for PROFIBUS DP
<b>(</b>	IC-KP2-2HB17-2V1D	IDENTControl Compact control interface with Ethernet interface for TCP/IP, PROFINET, EtherNet/IP, and MODBUS TCP protocols
	IC-KP2-2HB21-2V1D	Control interface unit IDENTControl Compact with EtherCAT interface

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".



Accessories				
	IUC76-F157-T17-M-FR1	Data carrier for standard applications		
	IUC76-F157-T18-M-FR1	Data carrier for paint shop applications		
102- 102- 102- 102- 102- 102- 102- 102-	IUC77-25L100-GBL 1000pcs	Data carrier		
1111	IUC77-28L90-M-FR1 25pcs	Data carrier		
•	IUC77-34-M-FR1 10pcs	Data carrier		
	IUC77-50-FR1 10pcs	Data carrier		
	IUZ-MH13	Mounting bracket for wall mounting		
	IUZ-MH15	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm		
d es	V1-G-2M-PUR-ABG-V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded		
1 es	V1-G-5M-PUR-ABG-V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded		
<i>6</i> 6	V1-G-10M-PUR-ABG- V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded		

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com