



Print mark contrast sensor DK10-LAS/35/49



- Laser print mark contrast sensor for recording very small print marks
- Laser class 2, eyesafe
- Adjustable sensitivity
- 30 µs response time, suitable for extremely rapid scanning

Print mark contrast sensor, 800 mm detection range, red laser light, laser class 2, light/dark on, sensitivity adjuster, NPN output, PNP output, M12 plug










Function

The contrast sensor series DK10, DK2X, DKE2X and DK3X have an extreme robust and IP67 tight industrial standard housing with eight M5 metal reinforced inserts for sensor mounting. The lenses are made of high grade glass. All sensors offer different light spot shapes and orientations and have powerful push-pull outputs (NPN/PNP/push-pull).

The DK10 sensor series offers laser and LED light sources, a manual sensitivity adjustment and high sensing ranges up to 800 mm.

The DK20/DK21/DKE2X standard contrast sensor series offers a very good contrast recognition and are available in extreme robust stainlesssteel housings (DKE).
The DK31/DK34/DK35 sensor series is designed for cutting edge contrast recognition at highest sensitivity level.
The series DK20/DK34 offer a static Teach-In, the DK21/DK21/DK31/DK35 series offer a dynamic Teach-In.

Dimensions




Technical Data

General specifications	
Sensor range	800 mm
Detection range	3 800 mm
Light source	laser diode
Light type	modulated visible red light
Laser nominal ratings	
Note	LASER LIGHT, DO NOT STARE INTO BEAM
Laser class	2
Wave length	650 nm
Beam divergence	< 1.5 mrad
Pulse length	1.5 μs
Repetition rate	108.7 kHz
max. pulse energy	2.1 nJ
Light spot representation	approx. 2 mm at a distance of 800 mm
Ambient light limit	
Continuous light	40000 Lux
Functional safety related parameters	
MTTF _d	550 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	60 %
Indicators/operating means	
Function indicator	LED yellow: lights up if receiver is lit (light on), lights up if receiver is not lit (dark on)

Technical Data Control elements Light-on/dark-on changeover switch, sensitivity adjuster **Electrical specifications** Operating voltage U_{B} 10 ... 30 V DC 10 % Ripple No-load supply current I_0 ≤ 55 mA Input Test input emitter deactivation with +Ub Output light/dark on switchable Switching type 1 PNP and 1 NPN short-circuit protected, open collector, synchronized-switching Signal output Switching voltage max. 30 V DC Switching current max. 200 mA f 16.5 kHz Switching frequency Response time 30 µs Conformity EN 60947-5-2 Product standard IEC 60825-1:2007 Laser safety Compliance with standards and directives Standard conformity Shock and impact resistance IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions Vibration resistance Approvals and certificates TR CU 020/2011 EAC conformity **UL** approval cULus Listed, Class 2 power source CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -10 ... 50 °C (14 ... 122 °F) Ambient temperature -20 ... 75 °C (-4 ... 167 °F) Storage temperature Mechanical specifications Housing width 33 mm Housing height 85.6 mm Housing depth 60.8 mm Degree of protection IP67 Connection 5-pin, M12 x 1 connector Material PC (glass-fiber-reinforced Makrolon) Housing Optical face glass Mass 200 g

Connection Assignment





Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)





Safety Information

Laser Class 2 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people!

Caution: Do not look into the beam!

Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Accessories					
6 /	V15-G-5M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey			
6/	V15-W-5M-PVC	Female cordset single-ended M12 angled A-coded, 5-pin, PVC cable grey			
++++	OMH-DK	Right-Angled Mounting Bracket			
# # ++	OMH-DK-1	Flat Mounting Bracket			

Switching threshold adjustment

The required switching threshold is adjusted with the sensitivity control. Please proceed as follows:

- 1. Switch the light/dark change-over switch to the light setting.
- 2. Point the light spot at the light part of the surface being scanned.
- 3. If the yellow indicator LED lights up, turn the sensitivity control to the left until the indicator LED goes off again. If the yellow indicator LED does not light up, miss out this step.
- 4. Turn the sensitivity control to the right until the indicator LED just lights up.
- 5. Point the light spot at the dark part of the surface being scanned.
- 6. The indicator LED must have gone off.
- 7. Turn the sensitivity control to the right again until the indicator LED lights up again. Counting the number of turns.
- 8. Turn the sensitivity control back to the left by half the number of counted turns.

Once the DK10 colour mark scanner has been adjusted in this way, the switching thres-hold is exactly in the middle of the measured light and dark values. The greater the number the number of times the sensitivity control is turned between the light and the dark marks, the greater the contrast.

Recommendation: The number of turns should be to > 0.5.

Switching mode adjustment:

Setting of light/dark switch	Receiver	Output PNP	Output NPN
Н	exposed	inactive	active
	unexposed	active	inactive
D	exposed	active	inactive
	unexposed	inactive	active