



Print mark contrast sensor DK21-9,5/110/124



- Diffuse mode sensor for recording any print mark
- Dynamic TEACH-IN: automatic switching threshold adaptation with one key pressure
- Optical system exchangeable by 90°
- 30 µs response time, suitable for extremely rapid scanning
- 3 emitter colors: green, red and blue

Print mark contrast sensor, 9.5 mm detection range, RGB light with rectangular light spot, external Teachin, push-pull output, M12 plug




Function

The contrast sensor series DK10, DK2X, DKE2X and DK3X have an extreme robust and IP67 tight industrial standard housing with eight M5 metal reinforced inserts for sensor mounting. The lenses are made of high grade glass. All sensors offer different light spot shapes and orientations and have powerful push-pull outputs (NPN/PNP/push-pull).


The DK10 sensor series offers laser and LED light sources, a manual sensitivity adjustment and high sensing ranges up to 800 mm.

The DK20/DK21/DKE2X standard contrast sensor series offers a very good contrast recognition and are available in extreme robust stainlesssteel housings (DKE).
The DK31/DK34/DK35 sensor series is designed for cutting edge contrast recognition at highest sensitivity level.
The series DK20/DK34 offer a static Teach-In, the DK21/DK21/DK31/DK35 series offer a dynamic Teach-In.

Dimensions



	sensor range 9.5 mm	sensor range 25 mm		
Standard	1 mm x 4 mm	2 mm x 8.5 mm		
Option /A	□ 4 mm x 1 mm	8.5 mm x 2 mm		
Option /B	O Ø1.5 mm	ø3 mm		




Technical Data

General specifications		
Sensor range		9.5 mm ± 3 mm
Light source		LED
Light type		Visible green/red/blue, modulated light
Light spot representation		rectangular 1 mm x 4 mm
Angle deviation		max. ± 3°
Ambient light limit		
Continuous light		7000 Lux
Teach-In		Dynamic Teach-In
Functional safety related parameters		
MTTF _d		650 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Function indicator		LED yellow; switching operation: lights up if print mark is detected Alarm display: flashing quickly, if no safe operation is possible
Control elements		Teach-In key
Electrical specifications		
Operating voltage	U_B	10 30 V DC
Ripple		10 %
No-load supply current	I_0	≤ 60 mA
Input		

yle e	.pai
1	Ę
000	8083
7	4
	ename:
E C	三 き
E 70	-04-04 -
- LO COCO	ZUZ3-04-04 FII
: L 70 70 0000 : -:::	II ISSUE: 2023-04-04 FII
EL 10 10 0000 :-::::::::::::::::::::::::::	5
II 10 10 0000	
C	-04-04 Date of
II 10 10 0000	2023-04-04 Date of
C	-04-04 Date of

Technical Data		
Technical Data		
Function input		Teach-In input
Output		
Signal output		Push-pull output, short-circuit protected, reverse polarity protected
Switching voltage		$PNP: \ge (+U_B - 2.5 \text{ V}), NPN: \le 1.5 \text{ V}$
Switching current		max. 200 mA
Switching frequency	f	16.5 kHz
Response time		30 μs
Conformity		
Product standard		EN 60947-5-2
Compliance with standards and directives		
Standard conformity		
Shock and impact resistance		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions
Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions
Approvals and certificates		
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-20 75 °C (-4 167 °F)
Mechanical specifications		
Housing width		33 mm
Housing height		85.6 mm
Housing depth		60.8 mm
Degree of protection		IP67
Connection		5-pin, M12 x 1 connector
Material		
Housing		PC (glass-fiber-reinforced Makrolon)
Optical face		glass
Mass		200 g

Connection Assignment




Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)



Accessories

6/	V15-G-5M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
6/	V15-W-5M-PVC	Female cordset single-ended M12 angled A-coded, 5-pin, PVC cable grey
H41 +	OMH-DK	Right-Angled Mounting Bracket
# # ++	OMH-DK-1	Flat Mounting Bracket

Adjustment

- Adjust light spot to background. The sensor must be bend 10° to 15° towards the material surface if the object surface is reflective or glossy.
- Keep Teach-In key at the device pressed or connect +UB to external input ET continuously. The Teach-In process starts 50 ms after the Teach-In signal is connected.
- The print mark must cover the light spot for at least 1 ms completely. Move the print mark through the light spot.
- The Teach-In process finishes 50 ms after the Teach-Insignal (keystroke or ET) with the following possible conditions:

Teach-In successful: the non-volatile saving of the taught-in values in EEPROM follows. Indicator-LED illuminates when print mark is detected. Push-pull output switches when print mark is detected to +UB, with background to 0 V. ALARM-function: Recorded contrast for all emitter light colours too faint. Indicator-LED flashes with approx. 4 Hz, optional analog-output shows minimal signal. Return to the operation mode with the latest accepted values after keystroke or +UB at ET (at least 50 ms).

The switching level is centered between the evaluated print mark/background-contrast values.

The sensor automatically selects and stores the most suitable emitter colour for the best print mark/background-contrast.

For exact contrast evaluation, the DK... can optionally be equipped with an additional analogue output.

Emitter-test function:

- Switch on sensor supply while active Teach-In signal (keystroke or ET). 1.
- After Teach-In is released, the green emitter is switched.
- 3. The red emitter is switched after the second Teach-In.
- 4. The blue emitter is switched after the third Teach-In.
- After the forth Teach-In: normal switching operation.

The switching of the output is suppressed during the test operation.

