



Retroreflective sensor RL91-6-IR/49/59/115



- Retroreflective sensor for single-beam closing edge protection
- Narrow housing suitable for small gaps
- Sturdy plastic housing
- Various possibilities for mounting
- Version with infrared light
- Version for supply voltage of up to 30 V DC
- Dark on version

Mid-range photoelectric sensors for detecting people, objects, and vehicles



Function


Concentration on the essentials is the hallmark of the 91 series. As ac/dc supply devices, these economical, reliable and easy-to-use photoelectric sensors can be used almost universally. Their narrow design means that they can be used in any environment. The single-beam photoelectric sensors of the 91 series are suitable for closing-edge monitoring for elevators, barriers and doors, as well as for object detection and object tracking in material handling systems.


Application

- Closing-edge monitoring for elevators, barriers and industrial doors
- · Detecting and tracking objects in material handling



Dimensions






		-			-
Iе	 	701			T .
	 		_	_	

General specifications		
Effective detection range		0 6 m
Reflector distance		0 6 m
Threshold detection range		9 m
Reference target		H85-2 reflector
Light source		LED
Light type		modulated infrared light
Diameter of the light spot		approx. 230 mm at a distance of 6000 mm
Opening angle		approx. 2.5 °
Ambient light limit		90000 Lux
Functional safety related parameters		
MTTF _d		1083.4 a
Indicators/operating means		
Function indicator		LED red, flashes when falling short of the operating reserve
Electrical specifications		
Operating voltage	U_B	12 30 V DC
No-load supply current	I_0	< 100 mA
Output		
Switching type		dark-on
Signal output		1 NPN, 1 PNP synchronized-switching, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC


Technical Data				
0 111		000 4		
Switching current		200 mA		
Switching frequency	f	25 Hz		
Response time		20 ms		
Conformity				
Product standard		EN 60947-5-2		
Approvals and certificates				
UL approval		cULus For overcurrent protection, install a fuse with a rated current of max. 5 A and min. 30 V DC $$		
CCC approval		CCC approval / marking not required for products rated ≤36 V		
Ambient conditions				
Ambient temperature		-20 55 °C (-4 131 °F)		
Storage temperature		-20 75 °C (-4 167 °F)		
Mechanical specifications				
Degree of protection		IP65		
Connection		5 m fixed cable		
Material				
Housing		Luran®		
Optical face		Luran®		
Mass		100 g		

Connection Assignment




- O = Light on
- = Dark on


Assembly



- 1 Functional display red
- 2 Optical axis Receiver
- 3 Optical axis Transmitter

Characteristic Curve





Accessories



Release date: 2022-11-18 Date of issue: 2022-11-18 Filename: 419059_eng.pdf

System Description

System Description

The retro-reflective sensor contains both an emitter and a receiver in a single housing. A reflector reflects the light from emitter back to the receiver. If an object interrupts the light beam, the switching function is initiated.