



# Retroreflective sensor RL91-6-IR/49/59/73c



- Retroreflective sensor for single-beam closing edge protection
- Narrow housing suitable for small gaps
- Sturdy plastic housing
- Various possibilities for mounting
- Version with infrared light
- Version for supply voltage of up to 30 V DC
- Dark on version

Mid-range photoelectric sensors for detecting people, objects, and vehicles



### **Function**


Concentration on the essentials is the hallmark of the 91 series. As ac/dc supply devices, these economical, reliable and easy-to-use photoelectric sensors can be used almost universally. Their narrow design means that they can be used in any environment. The single-beam photoelectric sensors of the 91 series are suitable for closing-edge monitoring for elevators, barriers and doors, as well as for object detection and object tracking in material handling systems.


### **Application**


- Closing-edge monitoring for elevators, barriers and industrial doors
- · Detecting and tracking objects in material handling



### **Dimensions**








# **Technical Data**

General specifications		
Effective detection range		0 6 m
Reflector distance		0 6 m
Threshold detection range		9 m
Reference target		H85-2 reflector
Light source		LED
Light type		modulated infrared light
Diameter of the light spot		approx. 230 mm at a distance of 6000 mm
Opening angle		approx. 2.5 °
Ambient light limit		90000 Lux
Functional safety related parameters		
MTTF <sub>d</sub>		1083.4 a
Indicators/operating means		
Function indicator		LED red, flashes when falling short of the operating reserve
Electrical specifications		
Operating voltage	$U_B$	12 30 V DC
No-load supply current	I <sub>0</sub>	< 100 mA
Output		
Switching type		dark-on
Signal output		1 NPN, 1 PNP synchronized-switching, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC

Switching current		200 mA
Switching frequency	f	25 Hz
Response time		20 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-20 55 °C (-4 131 °F)
Storage temperature		-20 75 °C (-4 167 °F)
Mechanical specifications		
Degree of protection		IP65
Connection		4-pin, M12 x 1 connector
Material		
Housing		Luran®
Optical face		Luran <sup>®</sup>
Mass		100 g

# **Connection Assignment**



- O = Light on
- = Dark on

## **Connection Assignment**




# **Connection Assignment**

Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)


## **Assembly**



- 1 Functional display red
- 2 Optical axis Receiver
- 3 Optical axis Transmitter

## **Characteristic Curve**





## **Accessories**

OMH-91	Mounting bracket

# Release date: 2022-11-18 Date of issue: 2022-11-18 Filename: 419060\_eng.pdf

## **System Description**

### **System Description**

The retro-reflective sensor contains both an emitter and a receiver in a single housing. A reflector reflects the light from emitter back to the receiver. If an object interrupts the light beam, the switching function is initiated.