

# Retroreflective sensor

## OBR5000-18GK40A-E0



- Short design in M18 plastic housing
- Not sensitive to ambient light
- Degree of protection IP67
- Very high detection range


### Retroreflective sensor



### Function

The optical sensors of this series have an M18 threaded housing that is optionally available in plastic or metal. The sensors are robust and versatile. Focusing on the essential requirements simplifies selection and commissioning, saving time and costs.

### Dimensions



### Technical Data

| General specifications     |                             |
|----------------------------|-----------------------------|
| Effective detection range  | 0 ... 5 m                   |
| Reflector distance         | 0 ... 5 m                   |
| Threshold detection range  | 7 m                         |
| Reference target           | reflector C110-2            |
| Light source               | LED                         |
| Light type                 | modulated visible red light |
| Polarization filter        | yes                         |
| Diameter of the light spot | approx. 270 mm at 5 m       |
| Opening angle              | approx. 2.6 °               |
| Optical face               | lateral                     |
| Ambient light limit        | EN 60947-5-2 40000 Lux      |

Release date: 2022-05-12 Date of issue: 2022-05-12 Filename: 70113328-100082\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PF** PEPPERL+FUCHS


## Technical Data

| Functional safety related parameters |                |                                                                                                                                            |
|--------------------------------------|----------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| MTTF <sub>d</sub>                    |                | 1552 a                                                                                                                                     |
| Mission Time (T <sub>M</sub> )       |                | 20 a                                                                                                                                       |
| Diagnostic Coverage (DC)             |                | 0 %                                                                                                                                        |
| Indicators/operating means           |                |                                                                                                                                            |
| Operation indicator                  |                | LED green:<br>on - power on<br>flashing (4 Hz) - short circuit                                                                             |
| Function indicator                   |                | Yellow LED:<br>Permanently lit - light path clear<br>Permanently off - object detected<br>Flashing (4 Hz) - insufficient operating reserve |
| Electrical specifications            |                |                                                                                                                                            |
| Operating voltage                    | U <sub>B</sub> | 10 ... 30 V DC                                                                                                                             |
| Ripple                               |                | max. 10 %                                                                                                                                  |
| No-load supply current               | I <sub>0</sub> | < 25 mA                                                                                                                                    |
| Protection class                     |                | III                                                                                                                                        |
| Output                               |                |                                                                                                                                            |
| Switching type                       |                | Q - Pin4: NPN normally open / dark-on                                                                                                      |
| Signal output                        |                | 1 NPN output, short-circuit protected, reverse polarity protected, open collector                                                          |
| Switching voltage                    |                | max. 30 V DC                                                                                                                               |
| Switching current                    |                | max. 100 mA , resistive load                                                                                                               |
| Voltage drop                         | U <sub>d</sub> | ≤ 1.5 V DC                                                                                                                                 |
| Switching frequency                  | f              | 500 Hz                                                                                                                                     |
| Response time                        |                | ≤ 1 ms                                                                                                                                     |
| Conformity                           |                |                                                                                                                                            |
| Product standard                     |                | EN 60947-5-2                                                                                                                               |
| Approvals and certificates           |                |                                                                                                                                            |
| UL approval                          |                | E87056 , cULus Listed , class 2 power supply , type rating 1                                                                               |
| Ambient conditions                   |                |                                                                                                                                            |
| Ambient temperature                  |                | -40 ... 60 °C (-40 ... 140 °F)                                                                                                             |
| Storage temperature                  |                | -40 ... 70 °C (-40 ... 158 °F)                                                                                                             |
| Mechanical specifications            |                |                                                                                                                                            |
| Degree of protection                 |                | IP67                                                                                                                                       |
| Connection                           |                | 2 m fixed cable                                                                                                                            |
| Material                             |                |                                                                                                                                            |
| Housing                              |                | PC (Polycarbonate)                                                                                                                         |
| Optical face                         |                | PMMA                                                                                                                                       |
| Cable                                |                | PVC                                                                                                                                        |
| Mass                                 |                | approx. 56 g                                                                                                                               |



## Connection





**Indication**



**Characteristic Curve**











**Accessories**

|                                                                                     |                 |                                  |
|-------------------------------------------------------------------------------------|-----------------|----------------------------------|
|  | <b>BF 18</b>    | Mounting flange, 18 mm           |
|  | <b>CPZ18B03</b> | Mounting Bracket with swivel nut |

Release date: 2022-05-12 Date of issue: 2022-05-12 Filename: 70113328-100082\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Accessories

|                                                                                   |                    |                                                                                   |
|-----------------------------------------------------------------------------------|--------------------|-----------------------------------------------------------------------------------|
|  | <b>BF 18-F</b>     | Plastic mounting adapter, 18 mm                                                   |
|  | <b>BF 5-30</b>     | Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm |
|  | <b>OMH-04</b>      | Mounting aid for round steel $\varnothing$ 12 mm or sheet 1.5 mm ... 3 mm         |
|  | <b>REF-H85-2</b>   | Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes                          |
|  | <b>REF-C110-2</b>  | Reflector, round $\varnothing$ 84 mm, central mounting hole                       |
|  | <b>REF-H50</b>     | Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap                |
|  | <b>REF-VR10</b>    | Reflector, rectangular 60 mm x 19 mm, mounting holes                              |
|  | <b>OFR-100/100</b> | Reflective tape 100 mm x 100 mm                                                   |