



# Print mark contrast sensor DK20-2497(/49)





- Diffuse mode sensor for recording any print mark
- Static TEACH-IN: automatic switching threshold adaptation
- 30 µs response time, suitable for extremely rapid scanning
- 3 emitter colors: green, red and blue

Print mark contrast sensor with plastic lens, 9.5 mm detection range, RGB light, light/dark on, external Teach-in, NPN output, PNP output, M12 plug




### **Dimensions**






#### Technical Data **General specifications** Sensor range $9.5 \text{ mm} \pm 3 \text{ mm}$ Light source I FD Visible green/red/blue, modulated light Light type Light spot representation rectangular 1 mm x 4 mm, Angle deviation max. ± 3° Ambient light limit Continuous light 7000 Lux Teach-In static Teach-In Functional safety related parameters $MTTF_d$ 650 a Mission Time (T<sub>M</sub>) 20 a 0 % Diagnostic Coverage (DC) Indicators/operating means LED yellow; switching operation: lights up if print mark is detected Teach-In operation: flashing slowly Function indicator alarm display: flashing quickly, if no safe operation is possible Control elements Teach-In key **Electrical specifications** Operating voltage $\mathsf{U}_\mathsf{B}$ 10 ... 30 V DC 10 % Ripple No-load supply current ≤ 70 mA Input Function input Teach-In input Output Switching type light/dark on switchable, results from the order of the Teach-In Signal output 1 PNP and 1 NPN short-circuit protected, open collector, synchronized-switching Switching voltage $PNP: \ge (+U_B - 2.5 \text{ V}), NPN: \le 1.5 \text{ V}$ max. 200 mA Switching current 16.5 kHz Switching frequency Response time 30 µs Conformity Product standard EN 60947-5-2 Compliance with standards and directives Standard conformity Shock and impact resistance IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions Vibration resistance IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions Approvals and certificates TR CU 020/2011 EAC conformity **UL** approval cULus Listed, Class 2 power source CCC approval / marking not required for products rated ≤36 V CCC approval **Ambient conditions** Ambient temperature -20 ... 60 °C (-4 ... 140 °F) Storage temperature -20 ... 75 °C (-4 ... 167 °F) Mechanical specifications Housing width 33 mm Housing height 85.6 mm Housing depth 60.8 mm Degree of protection IP67 Connection 5-pin, M12 x 1 connector Material PC (glass-fiber-reinforced Makrolon) Housing Optical face plastic 200 g Mass



## **Connection Assignment**





Λ		SS		141	_	c
	L.	 -	1 <b>.</b> .		_	٠.

	V15-G-5M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
	V15-W-5M-PVC	Female cordset single-ended M12 angled A-coded, 5-pin, PVC cable grey
H44 +	OMH-DK	Right-Angled Mounting Bracket
I I	OMH-DK-1	Flat Mounting Bracket

### Adjustment

- Adjust light spot to print mark. In case of mirroring or shiny object surface tilt Sensor by 10° ... 15°.
- Press Teach-In key, or apply a positive pulse (+UB) for at least 50 ms to the external Teach-In input. Now the indication LED flashes slowly (approx. 1 Hz).
- Adjust light spot to the background
- Press Teach-In key, or apply a positive pulse (+UB) for at least 50 ms to the external Teach-In input once more.
- Teach-In successful: sensor in switching mode, LED is

Alarme-function: contrast for all emitter colours too weak; a reliable sensor operation cannot be guaranteed. Indicator LED flashes quickly (approx. 4 Hz). Return to switch mode by keystroke.

The switching level is centered between the evaluated print mark/background-contrast values.

The sensor automatically selects and stores the most suitable emitter colour for the best print mark/backgroundcontrast.

For exact contrast evaluation, the DK... can optionally be equipped with an additional analogue output.

### Switching type:

The output switches at the receiver signal that has been first taught-in after +U<sub>B</sub>. The light-on/dark-on switching results from the changed sequence of the Teach-In procedure and is therefore reversible.


### **Emitter-test function:**

- Connection of +U<sub>B</sub> at active Teach-In signal (keystroke or ext. Teach-In).
- 2. After teach-in is finished (keystroke or ext. Teach-In signal) the green emitter is switched.
- 3. The red emitter is switched after the second Teach-In.
- The blue emitter is switched after the third Teach-In.
- After the forth Teach-In: switching operation

The switching of the output is suppressed during the test operation.



print-mark (bright)



print-mark (dark)

**EPPPERL+FUCHS**