Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 418101_eng.pdf

Print mark color sensor DF20/49/124




- Diffuse mode sensor for recording colored print marks on backgrounds with different colors
- TEACH-IN procedure for automatic threshold value setting
- 3 emitter colors: green, red and blue
- Very short response time
- Optical system exchangeable by 90°
- Sturdy, waterproof plastic housing


Print mark color sensor, 9.5 mm detection range, RGB light with rectangular light spot, external Teach-In, Teach-In button, NPN output, PNP output, M12 plug



Dimensions



	sensor range 9.5 mm	sensor range 25 mm
Standard	1 mm x 4 mm	2 mm x 8.5 mm
Option /A	□ 4 mm x 1 mm	8.5 mm x 2 mm
Option /B	○ ø1.5 mm	⊘ ø3 mm



Technical Data

General specifications $9.5 \text{ mm} \pm 2 \text{ mm}$ Sensor range Light source 3 LEDs (R,G,B) Visible green/red/blue, modulated light Light type Light spot representation rectangular 1 mm x 4 mm Angle deviation max. ± 3° Functional safety related parameters $MTTF_d$ 650 a 20 a Mission Time (T_M) Diagnostic Coverage (DC) 0 % Indicators/operating means Function indicator LED yellow, lights up if print mark is detected flashes, if no safe operation is possible Control elements Teach-In key **Electrical specifications** Operating voltage U_B 10 ... 30 V DC Ripple 10 % ≤ 55 mA No-load supply current In Input Function input Teach-In input Output Switching type PNP switches according to +U_B, NPN according to 0 V for detected mark Signal output 1 PNP and 1 NPN short-circuit protected, open collector, synchronized-switching Switching voltage PNP: \geq (+U_B -2.5 V), NPN: \leq 1.5 V Switching current max. 200 mA 1.65 kHz Switching frequency f Response time 300 μs Conformity EN 60947-5-2 Product standard Approvals and certificates CCC approval CCC approval / marking not required for products rated ≤36 V Approvals CF **Ambient conditions** Ambient temperature -20 ... 60 °C (-4 ... 140 °F)

-20 ... 75 °C (-4 ... 167 °F)


5-pin, M12 x 1 connector

33 mm

85.5 mm

60.8 mm

IP67





Storage temperature

Mechanical specifications

Housing width Housing height


Housing depth

Connection

Degree of protection

Print mark color sensor DF20/49/124

Connection Assignment




Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5 l	GY	(gray)



Accessories



V15-G-2M-PUR

Female cordset single-ended M12 straight A-coded, 5-pin, PUR cable grey

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Function

The colour sensor DF20 operates according to the "active three-range procedure". This means that its three transmission LEDs are switched one after the other and are evaluated individually. The light of the three different emitters is reflected from colored objects with different intensities. The reflected light of the individual emitters causes three different reception signals that are compared with the programmed (teach-in) values. Only if all three values (red, green and blue transmission light) correspond with the teach-in values both the switching outputs and the indicator LED will be activated. The reference values are stored in non-volatile memory and are thus available each time the DF20 is put into operation.

Arrangement

The device is equipped with an exchangeable optical system that can be screwed onto the front or the side of the print mark sensor depending on the application.

Setting

TEACH-IN procedure

Align the light spot to the print mark. For reflective or shiny objects, the sensor should be inclined to the surface of the material by 10° to 15°.

The TEACH-IN key on the device confirms whether a positive pulse (UB+) was present on the external TEACH-In input for at least 50 ms, the DF20 evaluates the reception signals of the individual transmitters and saves these in non-volatile memory. After the TEACH-IN signal is complete, the DF20 detects the programmed print mark and activates the two switching outputs. The display LED lights statically.

Alarm function

The display-LED of the DF20 flashes if no evaluation of the colour programmed with TEACH-IN is possible. You can return to switching operation by pressing a key or by using an external TEACH-IN signal.

Emitter test function

If an emitter test function needs to be performed, the TEACH-IN key must be held down while voltage is applied and then released again.

If the TEACH-IN key is pressed again, the green LED lights up, then the red LED during the next TEACH-IN and after that the blue LED. After testing the 3 transmission LEDs, the TEACH-IN key is pressed one more time and the device is back in switching operation with the last TEACH-IN values. Switching of outputs is suppressed in direct detection mode.