

# Retroreflective sensor RL91-6-IR/25/38a/115

- Retroreflective sensor for single-beam closing edge protection
- Narrow housing suitable for small gaps
- Sturdy plastic housing
- Various possibilities for mounting
- Version with infrared light
- Version for supply voltage of up to 30 V DC
- Light on version

Mid-range photoelectric sensors for detecting people, objects, and vehicles

# 

#### Function


Concentration on the essentials is the hallmark of the 91 series. As ac/dc supply devices, these economical, reliable and easy-to-use photoelectric sensors can be used almost universally. Their narrow design means that they can be used in any environment. The single-beam photoelectric sensors of the 91 series are suitable for closing-edge monitoring for elevators, barriers and doors, as well as for object detection and object tracking in material handling systems.

#### Application

- · Closing-edge monitoring for elevators, barriers and industrial doors
- · Detecting and tracking objects in material handling



#### **Dimensions**



#### **Technical Data**


General specifications		
Effective detection range		0 6 m
Reflector distance		0 6 m
Threshold detection range		9 m
Reference target		H85-2 reflector
Light source		LED
Light type		modulated infrared light
Diameter of the light spot		approx. 230 mm at a distance of 6000 mm
Opening angle		approx. 2.5 °
Ambient light limit		90000 Lux
Functional safety related parameters		
MTTF <sub>d</sub>		1083.4 a
Indicators/operating means		
Function indicator		LED red, flashes when falling short of the operating reserve
Electrical specifications		
Operating voltage	UB	12 30 V DC / 18 28 V AC
No-load supply current	I <sub>0</sub>	< 100 mA
Output		
Switching type		light-on
Signal output		Weak current relay, 1 alternator
Switching voltage		≤ 55 V AC / 24 V DC
Switching current		1 A /24 V DC, 0.5 A /110 V AC

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Technical Data		
Switching power		max. 24 W / 55 VA
Switching power	(	
Switching frequency	f	25 Hz
Response time		20 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus For overcurrent protection, install a fuse with a rated current of max. 5 A and min. 55 V AC $$
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-20 55 °C (-4 131 °F)
Storage temperature		-20 75 °C (-4 167 °F)
Mechanical specifications		
Degree of protection		IP65
Connection		5 m fixed cable
Material		
Housing		Luran®
Optical face		Luran®
Mass		100 g
Note		Safety fuse $\leq$ 315 mA (slow-blow) according to IEC 60127-2 Sheet 1 Recommendation: after a short circuit, check that the device is functioning correctly.

# **Connection Assignment**

Option:



#### Assembly



1	Functional display	red		
2	Optical axis Receiv	er		
3	Optical axis Transmitter			


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

3

## **Characteristic Curve**



## Accessories

# 

OMH-91	Mounting bracket

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

4

RL91-6-IR/25/38a/115

## **System Description**

#### **System Description**

The retro-reflective sensor contains both an emitter and a receiver in a single housing. A reflector reflects the light from emitter back to the receiver. If an object interrupts the light beam, the switching function is initiated.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

