

Retroreflective sensor RL91-54-RT/49/59/115

<u>[</u> {

- Retroreflective sensor for single-beam closing edge protection
- Narrow housing suitable for small gaps
- Sturdy plastic housing
- Various possibilities for mounting
- Version with red light
- Version for supply voltage of up to 30 V DC
- Dark on version

Mid-range photoelectric sensors for detecting people, objects, and vehicles

Function


Concentration on the essentials is the hallmark of the 91 series. As ac/dc supply devices, these economical, reliable and easy-to-use photoelectric sensors can be used almost universally. Their narrow design means that they can be used in any environment. The single-beam photoelectric sensors of the 91 series are suitable for closing-edge monitoring for elevators, barriers and doors, as well as for object detection and object tracking in material handling systems.

Application

- · Closing-edge monitoring for elevators, barriers and industrial doors
- · Detecting and tracking objects in material handling



Dimensions



Technical Data

General specifications		
Effective detection range		0 4 m
Reflector distance		0.2 4000 mm
Threshold detection range		8 m
Reference target		H85-2 reflector
Light source		LED
Light type		modulated visible red light
Diameter of the light spot		approx. 160 mm at a distance of 4000 mm
Opening angle		approx. 2.5 °
Ambient light limit		90000 Lux
Functional safety related parameters		
MTTF _d		1083.4 a
Indicators/operating means		
Function indicator		LED red, flashes when falling short of the operating reserve
Electrical specifications		
Operating voltage	U_B	12 30 V DC
No-load supply current	I ₀	< 100 mA
Output		
Switching type		dark-on
Signal output		1 NPN, 1 PNP synchronized-switching, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com




RL91-54-RT/49/59/115

_			
	chn	ical	
_	~		


Switching current		200 mA
Switching frequency	f	25 Hz
Response time		20 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus For overcurrent protection, install a fuse with a rated current of max. 5 A and min. 30 V DC
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-20 55 °C (-4 131 °F)
Storage temperature		-20 75 °C (-4 167 °F)
Mechanical specifications		
Degree of protection		IP65
Connection		5 m fixed cable
Material		
Housing		Luran®
Optical face		glass pane
Mass		100 g

Connection Assignment




O = Light on ● = Dark on

Assembly




1	Functional display	red	
2	Optical axis Receiver		
3	Optical axis Transm	nitter	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Characteristic Curve



Accessories

P	OMH-91	Mounting bracket

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

4

RL91-54-RT/49/59/115

System Description

System Description

The retro-reflective sensor contains both an emitter and a receiver in a single housing. A reflector reflects the light from emitter back to the receiver. If an object interrupts the light beam, the switching function is initiated.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

5