



Background suppression sensor RL28-8-H-2000-IR/47/105



- Ultra bright LEDs for power on and switching state
- Minimal black-white difference through the infrared transmission LED
- Not sensitive to ambient light, even with energy saving lamps
- Waterproof, degree of protection IP67
- Protection class II

Background suppression sensor











Dimensions



Technical Data

General specifications		00 0000	
Detection range		20 2000 mm	
Detection range min.		20 200 mm	
Detection range max.		20 2000 mm	
Background suppression		max. + 10 % of the upper limit of the detection range	
Light source		IRED	
Light type		modulated infrared light , 880 nm	
Black-white difference (6 %/90 %)		< 40 %	
Diameter of the light spot	approx. 70 mm at a distance of 2000 mm		
Opening angle		transmitter 2° receiver 2°	
Ambient light limit		50000 Lux	
Functional safety related parameters			
MTTF _d		720 a	
Mission Time (T _M)		20 a	
Diagnostic Coverage (DC)		0 %	
ndicators/operating means			
Operation indicator		LED green	
Function indicator		2 LEDs yellow ON: object inside the scanning range OFF: object outside the scanning range	
Control elements		Sensing range adjuster , Light-on/dark-on changeover switch	
Electrical specifications			
Operating voltage	U_{B}	10 30 V DC	
Ripple		10 %	
No-load supply current	I ₀	≤ 40 mA	
Output			
Switching type		light/dark on switchable	
Signal output		2 PNP, complementary, short-circuit protected, reverse polarity protected , open collectors	
Switching voltage		max. 30 V DC	
Switching current		max. 200 mA	
Switching frequency	f	250 Hz	
Response time		2 ms	
Conformity			
Product standard		EN 60947-5-2	
Approvals and certificates			
Protection class		II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1	
UL approval		E87056 , cULus Listed , class 2 power supply , type rating 1	
Ambient conditions			
Ambient temperature		-40 60 °C (-40 140 °F)	
Storage temperature		-40 60 °C (-40 140 °F)	
Mechanical specifications			
Housing width		25.8 mm	
Housing height		88 mm	
Housing depth		54.3 mm	
Degree of protection		IP67	
Connection		5-pin, M12 x 1 connector	
Material			
Housing		Plastic ABS	
Optical face		plastic	
Connector		plastic	
Mass		70 g	

Connection Assignment



- O = Light on
- = Dark on


Connection Assignment




Wire colors in accordance with EN 60947-5-2

1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)
5 GY (gray)

Characteristic Curve



Characteristic Curve



Application



Accessories		

-	

OMH-05 Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm



OMH-21 Mounting bracket: mounting aid for sensors in the RL* series



OMH-22 Mounting aid for RL* series



OMH-RLK29-HW Mounting bracket for rear wall mounting



OMH-RL28-C Weld slag cover model

Additional information

Intended use:

The transmitter and receiver are located in the same housing for direct detection sensors with background masking. Marking of objects outside the detection range is achieved by arranging the angle between the transmitter and receiver (2 receiver

Objects are detected independently of their surface structures, brightness and colour, as well as the brightness of the background.

Mounting instructions:

The sensors can be fastened directly with fixing screws or with a support bracket (not included with delivery).

The surface underneath must be flat to prevent the housing from moving when it is tightened into position. We recommend securing the nut and screw in place with spring washers to prevent the sensor from going out of adjustment.

Adjustment:

After the operating voltage is applied, the LED is lit green.

Align the sensor to the background. If the yellow LED is lit, the detection range should be reduced with the detection range adjuster until the yellow LED goes out.

Object direction:

Place the object to be detected at the desired maximum detection range and align the light spot to it. If the object is detected, the yellow LED lights up.

If it does not light up, the detection range must be adjusted on the potentiometer until it lights up when an object is detected. Cleaning:

We recommend cleaning the optical surface and checking the screwed connection and other connections at regular intervals.