



Ethernet switch managed gigabit ICRL-M-8RJ45/4SFP-G-DIN

- 8 Gigabit Ethernet RJ45 ports and 4 Gigabit SFP ports with DDM function
- Layer 2 Network Performance
- Redundant power input with an input power range of 10 to 36VDC
- IP20 with an extreme operating temperature range of -40 to 75°C
- Suitable for PROFINET IO and EtherNet/IP


Ethernet managed gigabit switch with 8 RJ45 and 4 SFP ports



Function

The ICRL-M-8RJ45/4SFP-G-DIN is a Gigabit industrial Ethernet Switch with eight RJ45 ports and four Gigabit SFP sockets for optical fiber network connection. It provides an Ethernet MAC controller with 24 Gbps Switch fabric bandwidth with 9K jumbo frame forwarding. The robust system design makes the switch survive under harsh outdoor environment with extreme electric magnetic interference and the variation of environment temperature. The switch also provides your network infrastructure with great performance and safety with network access control, and the ability to handle burst packets with smart buffer management for IP surveillance in real infrastructures.

Dimensions



Technical Data

General specifications

UL File Number	E185778
MTBF	69 years

Ethernet Interface

Connection type	RJ45 , SFP
Auto-MDI(-X)	yes

Release date: 2024-04-22 Date of issue: 2024-04-22 Filename: 70114058_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

Autonegotiation		yes
Ethernet Interface		Industrial Ethernet
Transfer rate		8 - 10BASE-T, 100BASE-TX, 1000BASE-T, 4 - SFP 100/1000 Mbps
Management		IPv4, IPv6, Console, HTTP, HTTPS, PortVision DX, SFTP, SNMP (v1, v2c, and v3), SSH, Telnet, TFTP
MIB		MIB-II, Bridge MIB, Ethernet-like-MIB, VLAN MIB, IGMP MIB, Private MIB
Monitoring		LLDP, Port Mirroring, RMON
Multicast		IGMP Query, IGMP Snooping, GMRP
Network performance		CFM, Jumbo Frames, QoS, CoSQueue Mapping, DSCP Priority Mapping
Network redundancy		STP, RSTP, MSTP, ERPS, Redundant Ring, LACP, Static Port Aggregation
Network services		DHCP Server (with Option 82), NTP, IEEE 1588 PTPv2 over UDP/IP
Notifications		E-Mail, Fault Relay, SNMP Traps, Syslog
Safety		RADIUS, TACACS+, DHCP Snooping, IP Source Guard, Dynamic ARP Inspection, MAC-Based Port Security
Traffic filtering		Storm Control (Broadcast, Multicast, and DLF), Rate Control, VLAN, Private VLAN, QinQ Tunneling, GVRP, IP Filtering, MAC Filtering, ARP Filtering
Cable type		Category 5e or better
Switch properties		
Hardware watchdog timer		10 s reset timer
MAC address table size		16K
Operating mode		Store and forward
Packet buffer size		1.5M Bytes shared memory for packet buffer with intelligent memory management unit for burst data traffic
Priority queues		8
VLAN entries		IEEE 802.1Q Tag VLAN with 256 VLAN Entries and provides 2K GVRP entries; 3 VLAN link modes- Trunk mode, Hybrid mode and Link access mode
SFP support		100BASE-FX Fiber, 1000BASE-SX/LX/LHX/XD/ZX
Standards		
IEEE 802.3 10BASE-T		yes
IEEE 802.3u 100BASE-TX		yes
IEEE 802.3x Flow Control and Back-pressure		yes
IEEE 802.1p Class of Service (CoS)		yes
IEEE 802.3ab 1000BASE-T		yes
IEEE 802.1AB Link Layer Discovery Protocol (LLDP)		yes
IEEE 802.1Q VLAN and GVRP		yes
IEEE 802.1D-2004 Rapid Spanning Tree Protocol (RSTP)		yes
IEEE 802.1s Multiple Spanning Tree Protocol (MSTP)		yes
IEEE 802.3ad Link Aggregation Protocol (LACP)		yes
IEEE802.1ad QinQ Tunneling		yes
IEEE 802.1x Port Based Network Access Protocol		yes
ITU-T G.8032 ERPS		yes
Indicators/operating means		
LED indication		see manual
Electrical specifications		
Rated operating voltage	U _e	10 ... 36 V DC
General information		Redundant power, digital output (relay output) rating 0.5A Max. @ 24V DC, Digital input
Nominal voltage		24 V DC
Inputs/Outputs		
Number/Type		8 x RJ45 , 4 x SFP
Directive conformity		

Release date: 2024-04-22 Date of issue: 2024-04-22 Filename: 70114058_eng.pdf


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.comUSA: +1 330 486 0001
fa-info@us.pepperl-fuchs.comGermany: +49 621 776 1111
fa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com
 **PEPPERL+FUCHS**

Technical Data

Electromagnetic compatibility		
Directive 2014/30/EU		EN 61000-6-2, IEC 61000-6-2 , EN 61000-6-4, IEC 61000-6-4
Standard conformity		
Electrical safety		CSA C22.2 No. 60950 / CSA C22.2 No. 60950/UL60950
Emitted interference		CISPR 22 , FCC Part 15 Subpart B Class A , EN61000-6-4, IEC61000-6-4
Noise immunity		EN61000-6-2, IEC61000-6-2
Ambient conditions		
Ambient temperature		-40 ... 75 °C (-40 ... 167 °F)
Storage temperature		-40 ... 85 °C (-40 ... 185 °F)
Relative humidity		max. 95 %
Altitude		0 ... 3048 m
Mechanical specifications		
Degree of protection		IP30
Connection		Power Supply Terminal Block (4-pin) Ethernet 8 x RJ45 , 4 x SFP
Material		
Housing		aluminium, black
Mass		1460 g
Dimensions		
Height		160 mm
Width		84 mm
Length		127 mm
Construction type		Cabinet module
Mounting		DIN rail or direct panel mounting

Connection



Release date: 2024-04-22 Date of issue: 2024-04-22 Filename: 70114058_eng.pdf

Indication

