Release date: 2023-05-09 Date of issue: 2023-05-09 Filename: 70131295-0005_eng.pdf

Inductive sensor

NBN3-F31K2M-Z8L-B23-S-3G-3D

- Direct mounting on standard actuators
- ATEX/IECEx Zone 2/22
- Compatible with all process control systems
- 2-wire DC sensor with minimum off-state current
- Rugged metal base
- Weatherproof housing for outdoor applications
- Plug-in terminals
- 1/2" NPT conduit entrance












Installation


The connections to this sensor are sealed with stopping plugs to protect against dirt and moisture. If not all of the connections are used in your application, then seal the remaining stopping plugs on the sensor permanently or check during initial installation and when performing regular maintenance work that the stopping plugs are secure and impermeable. If necessary, tighten the stopping plugs to a torque of 1 Nm.

Dimensions










Technical Data

Switching function		2 x normally open (NO)
Switching function		2 x normally open (NO)
Output type		Two-wire
Rated operating distance	Sn	2.5 mm
Installation		for non-flush mounting
Output polarity		DC
Assured operating distance	Sa	0 2.05 mm
Output type		2x 2-wire
Nominal ratings		
Operating voltage	U_B	6 30 V
Switching frequency	f	0 100 Hz
Hysteresis	Н	typ. 0.5 mm
Reverse polarity protection		reverse polarity tolerant
Short-circuit protection		no
Voltage drop	U_{d}	≤ 6 V
Operating current	IL	4 100 mA
Off-state current	l _r	100 200 μA typ. 160 μA
Functional safety related parameters		
MTTF _d		684 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Valve circuit		
Voltage		max. 32 V DC
Current		max. 240 mA
Short-circuit protection		no
Reverse polarity protection		yes, with reversed output LED is out of function, therfore more power for solenoid valv
Compliance with standards and directives		
Standard conformity		
Standards		EN IEC 60947-5-2:2020 IEC 60947-5-2:2019
Approvals and certificates		
IECEx approval		
Equipment protection level Gc		IECEx TUR 20.0062X
Equipment protection level Dc		IECEx TUR 20.0068X
ATEX approval		
Equipment protection level Gc		TÜV 20 ATEX 8592 X
Equipment protection level Dc		TÜV 20 ATEX 8598 X
Ambient conditions		
Ambient temperature		-40 75 °C (-40 167 °F) , restriction for use in hazardous area, see instruction manual
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		screw terminals
Connection (system side)		1/2" NPT cable gland , ground connection with earthing screw only for wire cross-section 4 mm², use solid wire or stranded wire with wire end ferrule
Connection (valve side)		screw terminal , Cable gland 1/2" NPT
Housing material		PC (glass-fiber-reinforced Makrolon)
Housing base		powder coated aluminum
Degree of protection		IP67; additional degree of protection IP66/IP69 with BT65-F31K2-RG-EN-01 and SH-F31K2-B13
Terminal assembly		
Number		10
Connection type		For connection of copper wires with 7 mm dismantle length Tightening torque 0.5 0.6 Nm

-
ō
Ġ
ō
Ë
Ψ
5
õ
0
Q
Ġ
Ø.
α
3
÷
0
/
œ.
ĕ
ਛ
2
ē
唐
щ
g
Ŷ
5
Ó
က်
Ø
8
N
œ.
sue
SS
of
a
ā
\Box
0
o
'n
Ö
φ
8
0
ā
a)
ate
쓩
0
eas
Œ
亩
Œ

Type Screw terminal block, pluggable Terminal capacity Conductor cross-section 0,25 2,5 mm², flexible/rigid For Multiple-wire connection: two wires of equal cross-section per 0.25	1 mm²
	1 mm²
Tightening torque, fastening screws 4 Nm 5 Nm	
Tightening torque, housing screws 1.5 Nm	
Tightening torque of cover srews 1.5 Nm	
Tightening torque, earthing screw 1.5 Nm	
Tightening torque, cable gland Refer to NEC (National Electrical Code), hand-tight then wrench tightened turns)	(max. 3
Tightening torque, stopping plug 2 Nm	
General information	
Use in the hazardous area see instruction manuals	

Connection



Accessories

B165-F31K2-HG-EN-01	Activator for F31K2 series including protective housing
SH-F31K2-B13	Protective cap for mechanically protected mounting
SH-BT65-F31K2-01	Protective housing for activator BT65-F31K2-RG-EN-01
BT115A	Activator for F31 series
BT115X	Activator for F31 series

5 PEPPERL+FUCHS