
# Release date: 2022-08-08 Date of issue: 2022-08-08 Filename: 803110\_eng.pdf

# E BUBYIO 28a-1455

# Photoelectric slot sensor

# GL5-L/28a/155





- High switching frequency
- Simple and fast mounting
- Clearly visible LED functional display




Miniature photoelectric slot sensor for the detection of small parts, L design, fork width 5 mm, infrared light, NPN outputs, flat connector




### **Function**

The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.

### **Dimensions**





## **Technical Data**

General specifications		
Light source		IRED
Light type		Infrared, continuous light , 940 nm
Target size		0.8 x 1.8 mm
Slot width		5 mm
Slot depth		8.5 mm
Ambient light limit		1000 Lux
Functional safety related parameters		
MTTF <sub>d</sub>		3760 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0 %
ndicators/operating means		
Function indicator		red LED lights up when receiving the light beam
Electrical specifications		
Operating voltage	U <sub>B</sub>	5 24 V DC , class 2
No-load supply current	I <sub>0</sub>	max. 20 mA
Time delay before availability	t <sub>v</sub>	< 2 ms
Output		
Switching type		light/dark on
Signal output		2 NPN complementary , overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 50 mA , resistive load
Voltage drop	U <sub>d</sub>	max. 0.2 V at 10 mA max. 0.6 V at 50 mA
Switching frequency	f	max. 5 kHz
Response time		40 μs Light beam is not interrupted 80 μs Light beam is interrupted
Repeat accuracy	R	0.03 mm
Compliance with standards and directives		
Directive conformity		
EMC Directive 2004/108/EC		EN 60947-5-2:2007+A1:2012
Standard conformity		
Standards		UL 60947-5-2
Approvals and certificates		
EAC conformity		TR CU 020/2011
UL approval		cULus Recognized, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-30 80 °C (-22 176 °F)
Pollution degree		2
Mechanical specifications		-
Housing width		19.5 mm
Housing height		26 mm
Degree of protection		IP50
Connection		4-pin flat connector
		τ μιτ παι συππεσιοι
Material		DRT
Housing		PBT
Mass		3 g

- O = Light on ● = Dark on
- . .

### **Accessories**




**CBL SET GL5** 

Connection cable for GL5 series

# **Response frequency**

The response frequency is the value when the disc, given in the figure below, is rotated.



### **Applications**

The GL5 is suited for applications in the semiconductor and electronic industrial environment.

Typical applications include:

- 1. Detection of lead frames
- 2. Detection of cam positions
- 3. Detection of limit positions of moving objects
- 4. Position detection of wafer cases