



Technical data

General specifications

Sensor range		SU18: 80 mm SU18/35: 280 mm SU19: 80 mm
Fiber optic length	l	2000 mm , adjustable
Fiber optic diameter	d	1.3 mm
Adapter form		00
End piece		thread
Bending radius		min. 25 mm
Fiber configuration	Fv	see dimensions
Angle of divergence		67 °
Accessories provided		Cutter for plastic fiber optics

Ambient conditions

Ambient temperature		-55 ... 70 °C (-67 ... 158 °F)
---------------------	--	--------------------------------

Mechanical specifications

Material		
Optical face		plastic
Sheathing		PVC
Core		plastic
End piece		Stainless steel 1.4305 / AISI 303

Model Number

KLR-C02-1,3-2,0-K84

Plastic fiber optic - diffuse
Threading M4

Features

- Thread M4

Series

Fiber optic amplifiers

Device series SU18 ; SU18/35 ; SU19

Description

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Accessories

OMH-LL-M4

Mounting bracket for fiber optic cable, M4 thread


KM4-0,5

Metal protection for plastic fiber optics M4 x 0.5 mm

KM4-1,0

Metal protection for plastic fiber optics M4 x 1.0 mm

Dimensions



Release date: 2015-04-14 11:51 Date of issue: 2015-04-14 805857_eng.xml