



**Technical data**

**General specifications**

Detection range		5 mm
Fiber optic length	l	2000 mm , adjustable
Fiber optic diameter	d	1.25 mm
Adapter form		00
End piece		Photoelectric slot sensor
Bending radius		min. 10 mm
Fiber configuration	Fv	see dimensions
Angle of divergence		67 °
Accessories provided		Cutter for plastic fiber optics

**Ambient conditions**

Ambient temperature		-55 ... 70 °C (-67 ... 158 °F)
---------------------	--	--------------------------------

**Mechanical specifications**

<b>Material</b>	
Optical face	plastic
Sheathing	PVC
Core	plastic
End piece	plastic

**General information**

Scope of delivery	Fiber optic cables packaged in pairs
-------------------	--------------------------------------

**Model Number**

**KLE-C02-1,25-2,0-K134**

Plastic fiber optic - thru-beam

**Features**

- Optimized for the detection of small parts
- 5 mm slot width

**Series**

**Fiber optic amplifiers**

Device series	SU18 ; SU18/35 ; SU19 ; ML17-LL
---------------	---------------------------------


**Description**

**Attention:**

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



**Dimensions**



Release date: 2014-07-09 15:35 Date of issue: 2014-07-09 805690\_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com