



Technical data

General specifications

Detection range		10 mm
Fiber optic length	l	2000 mm , adjustable
Fiber optic diameter	d	1.25 mm
Adapter form		00
End piece		Photoelectric slot sensor
Bending radius		min. 10 mm
Fiber configuration	Fv	see dimensions
Angle of divergence		67 °
Accessories provided		Cutter for plastic fiber optics

Ambient conditions

Ambient temperature		-55 ... 70 °C (-67 ... 158 °F)
---------------------	--	--------------------------------

Mechanical specifications

Material		
Optical face		plastic
Sheathing		PVC
Core		plastic
End piece		plastic

General information

Scope of delivery		Fiber optic cables packaged in pairs
-------------------	--	--------------------------------------

Model Number

KLE-C02-1,25-2,0-K135

Plastic fiber optic - thru-beam

Features

- Optimized for the detection of small parts
- 10 mm slot width

Series

Fiber optic amplifiers

Device series	SU18 ; SU18/35 ; SU19 ; ML17-LL
---------------	---------------------------------


Description

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Dimensions



Release date: 2014-07-09 15:35 Date of issue: 2014-07-09 805691_eng.xml