

Connection cable, Ethernet


V1SD-G-GN40M-PUR-E1S-V45-G

- Hard-wearing PUR cable
- Suitable for drag chains and abrasion resistant
- D coding for Ethernet
- Conforms to PROFINET
- CAT5/CAT5e cable
- Degree of protection IP68 / IP69
- Free of paint wetting interfering substances
- Halogen-free
- Specific design protects against loosening and inaccurate installation

Ethernet bus cable M12 plug straight D-coded to RJ45 Ethernet-coded, 4-pin, PUR cable green, Cat5e, shielded, drag chain suitable



Dimensions



Technical Data

General specifications

Connector 1			
Connection			plug
Construction type			M12
Style			straight
Locking			screw connection
Number of pins			4
Coding			D-coded
Connector 2			
Connection			plug
Construction type			RJ45
Style			straight
Locking			snap locking
Number of pins			8
Coding			EtherNet/IP / PROFINET

Electrical specifications

Operating voltage	U _B		max. 48 V AC / 60 V DC
-------------------	----------------	--	------------------------

Conformity

Degree of protection			EN 60529
Plug connection			connector M12 x 1 : IEC 61076-2-101 connector RJ45 : IEC 60603-7
Component category			CAT5 (IEC 11801) , CAT5e (IEC 61156-6)
Flammability			IEC 60332-1-2 / UL 2556 / ISO 6722-1 5.22 (UN ECE-R 118.01)

Release date: 2024-03-17 Date of issue: 2024-03-17 Filename: 70137389_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com




PEPPERL+FUCHS

Technical Data

Ambient conditions		
Ambient temperature		
Connector 1		-40 ... 90 °C (-40 ... 194 °F)
Cable, fixed		-30 ... 70 °C (-22 ... 158 °F)
Cable, flexing		-20 ... 70 °C (-4 ... 158 °F)
Mechanical specifications		
Connector 1		
Tightening torque		0.6 Nm
Loosening protection		available
Tool installation		straight knurling and hexagon nut SW = 14 mm
Mating cycles		min. 100
Shielding		shield connected to screw connection
Degree of protection		IP68 / IP69
Connector 2		
Loosening protection		available
Mating cycles		min. 100
Shielding		shield connected to connector
Degree of protection		IP20
Cable		
Sheath diameter		6 mm
Bending radius		> 10 x cable diameter, moving > 8 x cable diameter, fixed
Sheath stripping force		max. 60 N / 100 mm
Sheath color		green (similar to RAL 6018)
Number of cores		4
Core cross section		0.34 mm ² / 22 AWG
Cores color		Core 1-1: yellow Core 2-3: white Core 3-2: orange Core 4-6: blue
Core construction		7 x 0.254 mm Ø twisted quad
Shield		aluminum-lined polyester foil Tinned copper braiding
Length	L	40 m
Drag chain suitability		
Drag chain cycles		max. 1000000
Motion velocity		max. 3 m/s
Traverse distance		max. 5 m
Acceleration		max. 2 m/s ²
Material		
PWIS free		yes
Halogen-free		yes
Connector 1		
Screw connection		Zinc diecast, nickel-plated
Body		TPU, black
Contact surface		Au
Flammability		V-2
Connector 2		
Body		PA, green
Flammability		V-0
Cable		
Sheathing		PUR based on polyether
Core insulation		PP
Flammability		FT2 complies with UN ECE-R 118.01

Release date: 2024-03-17 Date of issue: 2024-03-17 Filename: 70137389_eng.pdf

Connection



Release date: 2024-03-17 Date of issue: 2024-03-17 Filename: 70137389_eng.pdf