# Release date: 2023-10-25 Date of issue: 2023-10-25 Filename: 70141166-100002\_eng.pdf

# Vibration sensor

# VIM62PL-E0T16-0ME-I420V14

- Extended temperature range
- Screw-in thread for simple installation
- Simple electrical commissioning
- Rugged stainless steel housing
- Detection of low frequency vibrations
- Additional output with measured temperature value
- Vibration velocity in mm/s via root mean square formation (rms)

Vibration sensor with analog current output and increased temperature resistance







# **Function**


The vibration sensor determines the vibration quantity using rms (root meas square) averaging. This form of quadratic averaging or pre-filtering enables precise trend statements about the condition of the application.

Furthermore, the vibration sensor has an additional output for the output of the measured temperature value.

The sensor's design is impressively robust against tough environmental conditions.

The stainless steel housing provides optimal protection against corrosion. The wide temperature range of the sensor enables reliable measured values even in harsh conditions.
The simple mounting allows for commissioning in any application.

# **Dimensions**




# **Technical Data**

General specifications		
Туре	Vibration sensor	
Measuring technology	MEMS	

Technical Data

## Series Performance Line Measured variable Vibration velocity Temperature Measurement range Vibration velocity 0 ... 16 mm/s rms -40 ... 125 °C (-40 ... 257 °F) Temperature $\pm\,0.1\,$ mm/s (calibration point: 90% of the measuring range; 159.2 Hz) Complies with the tolerance requirements of DIN ISO 2954 for measurement range Measurement accuracy greater than 8 mm/s < 5 % of the partial lateral acceleration, which acts exactly 90° to the measuring axis Cross-sensitivity 1 ... 1000 Hz Frequency range Averaging time for v-rms: 12 s Electrical specifications external fuse is required: 3 A, semi-time-lag, 30 V DC Fusing Operating voltage $U_{B}$ max. 50 mA Current consumption Power consumption $P_0$ max. 750 mW Time delay before availability $t_v$ 10 s (rms filter is calculated intially with measurement data before they are available at the output) Surge protection up to 2 kV Output 1 Output type analog output, current output of the vibration variable Output current 4 ... 20 mA Load resistor ≤ 500 Ω Output 2 Output type analog output, current output of the temperature Output current 4 ... 20 mA Load resistor < 500 O Standard conformity Degree of protection DIN EN 60529, IP66, IP67 DIN EN 60068-2-27, 60 g, 6 ms Shock resistance Vibration resistance DIN EN 60068-2-6, 16.5 g, 10 ... 1000 Hz Approvals and certificates **UL** approval $\rm E468231~cULus~Listed,~Class~III~Power~Source~and~limited~energy~,~if~UL~marking~is~marked~on~the~product.~For~use~in~NFPA~70~Applications~only.$ **Ordinary Location** adapters providing field wiring on request Maximum permissible ambient temperature max. 60 °C (max. 140 °F) **Ambient conditions** -40 ... 60 °C (-40 ... 140 °F) Ambient temperature -40 ... 125 °C (-40 ... 257 °F) directly at the mounting point Measuring head temperature Storage temperature -40 ... 60 °C (-40 ... 140 °F) **Mechanical specifications** Connection type plug Stainless steel 1.4305 / AISI 303 Housing material Housing length 82.35 mm Housing diameter 31 mm Degree of protection IP66 / IP67 only in connected state Connector M12 Threading Number of pins 4 Mass approx. 200 g

# Connection



# **Connection Assignment**



# **Accessories**

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.

# Installation

# **Further Documentation**

The sensor manual is also available as detailed overall documentation. Among other things, installation, grounding concepts and mounting are described there in detail.
You can access the manual via the product detail page at www.pepperl-fuchs.com.

The correct electrical connection and the selection of the appropriate grounding concept are crucial for malfunction-free operation of the sensor. For detailed information you may refer to the manual of the sensor.