

Miniature slot sensor for small part detection, L design, 5 mm slot width, infrared light, NPN output, light on, 150 mm fixed cable with JST plug, 3-pin



Function

The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.


Application


- · Detection of lead frames
- · Detection of cam positions
- · Detection of limit positions of moving objects
- · Position detection of wafer cases

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Dimensions





Technical Data


General specifications Light source IRED Light type Infrared, continuous light, 940 nm Target size 0.8 x 1.8 mm Slot width 5 mm Slot depth 8.5 mm 1000 Lux Ambient light limit Functional safety related parameters MTTF_d 3760 a Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0% Indicators/operating means Function indicator red LED lights up when receiving the light beam **Electrical specifications** Operating voltage 5 ... 24 V DC , class 2 U_B max. 20 mA No-load supply current \mathbf{I}_0 Time delay before availability t_v < 2 ms Output Switching type light-on Signal output 1 NPN , overvoltage protected Switching voltage max. 30 V DC Switching current max. 50 mA, resistive load U_{d} max. 0.2 V at 10 mA max. 0.6 V at 50 mA Voltage drop Switching frequency max. 5 kHz f

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2023-12-28 Date of issue: 2023-12-28 Filename: 816810_eng.pdf

Technical Data		
Response time		40 μs Light beam is not interrupted 80 μs Light beam is interrupted
Repeat accuracy	R	0.03 mm
Compliance with standards and directives		
Directive conformity		
EMC Directive 2004/108/EC		EN 60947-5-2:2007+A1:2012
Standard conformity		
Standards		UL 60947-5-2
Approvals and certificates		
UL approval		cULus Recognized, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-30 80 °C (-22 176 °F)
Pollution degree		2
Mechanical specifications		
Degree of protection		IP50
Connection		0.15 m cable with 3-pin JST connector
Material		
Housing		PBT
Mass		3 g
Tightening torque, fastening screws		0.6 Nm
Dimensions		
Height		26 mm
Width		18.5 mm
Length		15.5 mm
Cable length		0.15 m

Connection Assignment



Connection



 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Gr

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com


3

Connection

Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	BU	(blue)
3	BK	(black)

Technical Features



Response frequency The response frequency is the value when the disc is rotated, see figure.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



4