# Release date: 2023-12-28 Date of issue: 2023-12-28 Filename: 816825\_eng.pdf



# Photoelectric slot sensor GL5-U/46a/59/115e



- Miniature design
- Optimized for the detection of small parts
- High switching frequency
- Simple and fast mounting
- Clearly visible LED functional display

Miniature slot sensor for small part detection, U design, 5 mm slot width, infrared light, PNP output, dark on, 150 mm fixed cable with JST plug, 3-pin



### **Function**


The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.


### **Application**


- · Detection of lead frames
- · Detection of cam positions
- · Detection of limit positions of moving objects
- · Position detection of wafer cases



### **Dimensions**








### **Technical Data**

General specifications		
Light source		IRED
Light type		Infrared, continuous light , 940 nm
Target size		0.8 x 1.8 mm
Slot width		5 mm
Slot depth		8.5 mm
Ambient light limit		1000 Lux
Functional safety related parameters		
MTTF <sub>d</sub>		3760 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Function indicator		red LED lights up when receiving the light beam
Electrical specifications		
Operating voltage	U <sub>B</sub>	5 24 V DC , class 2
No-load supply current	$I_0$	max. 20 mA
Time delay before availability	t <sub>v</sub>	< 2 ms
Output		
Switching type		dark-on
Signal output		1 PNP , overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 50 mA, resistive load
Voltage drop	U <sub>d</sub>	max. 0.2 V at 10 mA max. 0.6 V at 50 mA

_	
8	
فَ	
ē	
Ω,	
82	
<u></u>	
Ö	
-llename: 816825_6	
ž	
<u>e</u>	
82	
Z0Z3-1Z-Z8 F	
Ξ	
2023	
3	
ssne:	
SS	
5	
<u>a</u>	
Da	
χ	
v	
5	
202	
Helease date: 2023-12-28 Date of Issue:	
<u>.</u>	
ga	
se	
eas	
ē	
-	

Technical Data		
Switching frequency	f	max. 5 kHz
Response time		40 μs Light beam is not interrupted 80 μs Light beam is interrupted
Repeat accuracy	R	0.03 mm
Compliance with standards and directives		
Directive conformity		
EMC Directive 2004/108/EC		EN 60947-5-2:2007+A1:2012
Standard conformity		
Standards		UL 60947-5-2
Approvals and certificates		
UL approval		cULus Recognized, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-30 80 °C (-22 176 °F)
Pollution degree		2
Mechanical specifications		
Degree of protection		IP50
Connection		0.15 m cable with 3-pin JST connector
Material		
Housing		PBT
Mass		3 g
Tightening torque, fastening screws		0.6 Nm
Dimensions		
Height		25.4 mm
Width		7 mm
Length		26.2 mm
Cable length		0.15 m

## **Connection Assignment**



### Connection




### **Connection**

Wire colors in accordance with EN 60947-5-2

2 BU (blue) 3 BK (black)

## **Technical Features**



Response frequency
The response frequency is the value when the disc is rotated, see figure.