



**Technical data**

**General specifications**

Detection range		SU18: 70 mm SU18/35: 300 mm SU19: 70 mm
Fiber optic length	l	2000 mm , adjustable
Fiber optic diameter	d	1 mm
Adapter form		00
End piece		thread
Bending radius		min. 15 mm
Fiber configuration	Fv	see dimensions
Angle of divergence		67 °
Accessories provided		Cutter for plastic fiber optics

**Ambient conditions**

Ambient temperature		-55 ... 70 °C (-67 ... 158 °F)
---------------------	--	--------------------------------

**Mechanical specifications**

Material		
Optical face		plastic
Sheathing		PVC
Core		plastic
End piece		Stainless steel 1.4305 / AISI 303

**General information**

Scope of delivery		Fiber optic cables packaged in pairs
-------------------	--	--------------------------------------

**Model Number**

**KLE-C04-1,0-2,0-K104**  
 Plastic fiber optic - thru-beam  
 Threading M3

**Features**

- Thread M3

**Series**

**Fiber optic amplifiers**

Device series	SU18 ; SU18/35 ; SU19 ; ML17-LL
---------------	---------------------------------

**Description**


**Attention:**  
 Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



**Accessories**

- OMH-LL-M3**  
Mounting bracket for fiber optic cable, M3 thread
- KM3-0,5**  
Metal protection for plastic fiber optics M3 x 0.5 m
- KM3-1,0**  
Metal protection for plastic fiber optics M3 x 1.0 m

**Dimensions**



Release date: 2014-07-09 15:35 Date of issue: 2014-07-09 805841\_eng.xml