Release date: 2023-05-12 Date of issue: 2023-05-12 Filename: 806116_eng.pdf

60 4

Photoelectric slot sensor GL5-R/43a/115



- Miniature design
- Optimized for the detection of small parts
- High switching frequency
- Simple and fast mounting
- Clearly visible LED functional display

Miniature photoelectric slot sensor for the detection of small parts, R design, fork width 5 mm, infrared light, PNP outputs, fixed cable



Function


The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.


Application

- Detection of lead frames
- · Detection of cam positions
- · Detection of limit positions of moving objects
- · Position detection of wafer cases



Dimensions





Technical Data

General specifications		
Light source		IRED
Light type		Infrared, continuous light , 940 nm
Target size		0.8 x 1.8 mm
Slot width		5 mm
Slot depth		8.5 mm
Ambient light limit		1000 Lux
Functional safety related parameters		
MTTF _d		3760 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Function indicator		red LED lights up when receiving the light beam
Electrical specifications		
Operating voltage	U_B	5 24 V DC , class 2
No-load supply current	I_0	max. 20 mA
Time delay before availability	t _v	< 2 ms
Output		
Switching type		light/dark on
Signal output		2 PNP complementary , overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 50 mA, resistive load
Voltage drop	U_{d}	max. 0.2 V at 10 mA max. 0.6 V at 50 mA
Switching frequency	f	max. 5 kHz

Technical Data

0.03 mm

Compliance with standards and directives

EN 60947-5-2:2007+A1:2012

Standard conformity

Standards UL 60947-5-2

Approvals and certificates

UL approval cULus Recognized, Class 2 Power Source

R

CCC approval / marking not required for products rated ≤36 V CCC approval

13.2 mm

2 m

Ambient conditions

-25 ... 55 °C (-13 ... 131 °F) Ambient temperature -30 ... 80 °C (-22 ... 176 °F) Storage temperature

Pollution degree

Mechanical specifications Housing width

Housing height 13.4 mm Degree of protection IP50

Connection 2 m cable, 4 x 0.08 mm², PVC


Material

Cable length

Housing PBT Mass 25 g


Tightening torque, fastening screws 0.6 Nm

Connection Assignment



O = Light on

Release date: 2023-05-12 Date of issue: 2023-05-12 Filename: 806116_eng.pdf



 $\begin{tabular}{ll} \textbf{Response frequency}\\ \textbf{The response frequency is the value when the disc is rotated, see figure.} \end{tabular}$