# Release date: 2023-05-12 Date of issue: 2023-05-12 Filename: 806118\_eng.pdf

# Photoelectric slot sensor GL5-F/28a/115





- Miniature design
- Optimized for the detection of small parts
- High switching frequency
- Simple and fast mounting
- Clearly visible LED functional display

Miniature photoelectric slot sensor for the detection of small parts, F design, fork width 5 mm, infrared light, NPN outputs, fixed cable



### **Function**


The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.

### **Application**

- Detection of lead frames
- · Detection of cam positions
- · Detection of limit positions of moving objects
- · Position detection of wafer cases



### **Dimensions**




## **Technical Data**

| General specifications               |         |   |
|--------------------------------------|---------|---|
| Light source                         |         | IRED  |
| Light type                           |         | Infrared, continuous light , 940 nm             |
| Target size                          |         | 0.8 x 1.8 mm                                    |
| Slot width                           |         | 5 mm  |
| Slot depth                           |         | 8.5 mm  |
| Ambient light limit                  |         | 1000 Lux  |
| Functional safety related parameters |         |   |
| MTTF <sub>d</sub>                    |         | 3760 a  |
| Mission Time (T <sub>M</sub> )       |         | 20 a  |
| Diagnostic Coverage (DC)             |         | 0 %   |
| Indicators/operating means           |         |   |
| Function indicator                   |         | red LED lights up when receiving the light beam |
| Electrical specifications            |         |   |
| Operating voltage                    | $U_B$   | 5 24 V DC , class 2                             |
| No-load supply current               | $I_0$   | max. 20 mA                                      |
| Time delay before availability       | $t_{v}$ | < 2 ms  |
| Output                               |         |   |
| Switching type                       |         | light/dark on                                   |
| Signal output                        |         | 2 NPN complementary , overvoltage protected     |
| Switching voltage                    |         | max. 30 V DC                                    |
| Switching current                    |         | max. 50 mA, resistive load                      |
| Voltage drop                         | $U_{d}$ | max. 0.2 V at 10 mA max. 0.6 V at 50 mA         |
| Switching frequency                  | f       | max. 5 kHz                                      |
|                                      |         |   |

| Technical Data                           |   |  |
|--|---|--|
| Response time                            |   | 40 μs Light beam is not interrupted                          |
| . 135po.135 ti13                         |   | 80 μs Light beam is interrupted                              |
| Repeat accuracy                          | R | 0.03 mm  |
| Compliance with standards and directives |   |  |
| Directive conformity                     |   |  |
| EMC Directive 2004/108/EC                |   | EN 60947-5-2:2007+A1:2012                                    |
| Standard conformity                      |   |  |
| Standards                                |   | UL 60947-5-2   |
| Approvals and certificates               |   |  |
| UL approval                              |   | cULus Recognized, Class 2 Power Source                       |
| CCC approval                             |   | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions                       |   |  |
| Ambient temperature                      |   | -25 55 °C (-13 131 °F)                                       |
| Storage temperature                      |   | -30 80 °C (-22 176 °F)                                       |
| Pollution degree                         |   | 2  |
| Mechanical specifications                |   |  |
| Housing width                            |   | 13.2 mm  |
| Housing height                           |   | 13.4 mm  |
| Degree of protection                     |   | IP50   |
| Connection                               |   | $2 \text{ m cable}$ , $4 \times 0.08 \text{ mm}^2$ , PVC     |
| Material                                 |   |  |
| Housing                                  |   | PBT  |
| Mass                                     |   | 25 g   |
| Tightening torque, fastening screws      |   | 0.6 Nm   |
| Cable length                             |   | 2 m  |
|  |   |  |

# **Connection Assignment**





Response frequency
The response frequency is the value when the disc is rotated, see figure.