



Mounting aid MH-18GMA


- Low profile
- Integral O-ring seal
- Press-fit sensor installation

Mounting flange for 18 mm diameter, right-angle ultrasonic sensors

Dimensions







Technical Data

Mechanical specifications	
Material	Sarlink® 5775B 75, fully cross-linked TPV, UV stabilized
Tightening torque	2 Nm
Mounting	Hardware includes 3 each of the following: M5 x 20 mm socket-cap stainless steel screws Stainless steel washers , Stainless steel nuts
General information	
Supplementary information	For use with the following sensors: UBE1000-18GM40A-SE2-V1 UB300-18GM40A-E4-V1 UB300-18GM40A-E5-V1 UB300-18GM40A-U-V1 UB800-18GM40A-E4-V1 UB800-18GM40A-E5-V1 UB800-18GM40A-I-V1 UB800-18GM40A-I-V1 UB800-18GM40A-U-V1



Product Description

The MH-18GMA flange accommodates all right angle-sensing, 18 mm diameter ultrasonic sensors.

Installation Instructions

1.) Install an M12 cordset onto the sensor's connector (Figure 1).



Figure 1

- 2.) Stabilize the MH-18GMA (i.e., within the palm of your hand—Figure 2).
- 3.) Hold the sensor at the connector with your other hand and press the transducer end of the sensor into the flange (Figure 2). Push the sensor into the flange until the white transducer is centered in the flange opening (Figure 3).

IMPORTANT: The compression fit is intentionally tight. A firm installation force is required.





Figure 2

Figure 3