


Retroreflective sensor with polarization filter, plastic housing, 5 m detection range, red light, sensitivity adjuster, light/dark on, DC version, PNP output, fixed cable



Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

Technical Data

General specifications		
Effective detection range		05 m
Reflector distance		0.01 5 m
Threshold detection range		7 m
Reference target		H50 reflector
Light source		LED
Light type		modulated visible red light
Polarization filter		yes
Diameter of the light spot		approx. 500 mm at a distance of 7 m
Opening angle		approx. 4 °
Optical face		frontal
Ambient light limit		EN 60947-5-2:2007+A1:2012
Functional safety related parameters		EN 00947-9-2.2007 FAI.2012
MTTF _d		860 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0%
Indicators/operating means		0 %
Operation indicator		LED green: power on LED yellow: switching state
Control elements		sensitivity adjustment
Control elements		• •
Electrical specifications		Light-on/dark-on changeover switch
	U _B	10 30 V DC
Operating voltage Ripple	Ο _B	max. 10 %
No-load supply current	lo	< 20 mA
Output	10	< 20 IIA
Switching type		The switching type of the sensor is adjustable. The default setting is: light-on
•		
Signal output Switching voltage		1 PNP output, short-circuit protected, reverse polarity protected, open collector max. 30 V DC
Switching current		max. 30 v DC max. 100 mA , resistive load
Voltage drop	U _d	≤ 1.5 V DC
	f	500 Hz
Switching frequency Response time	1	1 ms
Conformity		1115
Product standard		EN 60947-5-2
Approvals and certificates		EN 00947-3-2
••		al II up Listed Class 2 Dower Source or listed Dower Supply with a limited valtage
UL approval		cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-30 60 °C (-22 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		11 mm
Housing height		31 mm
Housing depth		20 mm
Degree of protection		IP67
Connection		2 m fixed cable
Material		
Housing		PC (Polycarbonate)
Optical face		РММА
Mass		approx. 50 g
Tightening torque, fastening screws		0.6 Nm
Cable length		2 m


 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get


 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com




Assembly



1	Light-Dark-switching	
2	Sensitivity adjuster	
3	Signal display	yellow
4	Operating display	green

Characteristic Curve




Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3

ML100-55-6086/103

Characteristic Curve



Accessories

0	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
* *	OMH-F10-ML100	Mounting aid for ML100 series
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket
	OMH-10	Mounting aid for ML100 series
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole
	REF-H60-2	Reflector with mounting holes
	REF-H33	Reflector with screw fixing

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 813877_eng.pdf

Accessories					
	OFR-70-2	Reflective tape 70 mm x 70 mm			
	REF-MH23-2	Reflector with Micro-structure, rectangular 23 mm x 14 mm, diagonal mounting hole			
	OMH-ML100-S1	Mounting bracket			
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes			
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap			
	OFR-100/100	Reflective tape 100 mm x 100 mm			

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group www.pepperl-fuchs.com

5