

Glass Fiber Optic Cables

Thru-Beam Mode Glass Fiber Optic Cables
for OCT300-M1K and VL18LL Sensors

Right Angle Sensing Head						
Model Number	Cable Length	Fiber Diameter	Sheathing Material	Compatible Sensors	Sensing Range	Dimensions (mm)
LCE 18-2.3-0.5-K9	0.5 m	2.3 mm	PVC	OJ500-M1K	830 mm	
				OCT500-M1A	830 mm	
				OCT300-M1K	240 mm	
				VL18LL	240 mm	
LSE 18-1.1-0.5-K9	0.5 m	1.1 mm	Silicone	OJ500-M1K	275 mm	
				OCT500-M1A	275 mm	
				OCT300-M1K	97 mm	
				VL18LL	89 mm	
LME 18-1.9-0.5-K9	0.5 m	1.9 mm	Stainless Steel	OJ500-M1K	1050 mm	
				OCT500-M1A	1050 mm	
				OCT300-M1K	310 mm	
				VL18LL	270 mm	
LME 18-2.3-0.5-K10	0.5 m	2.3 mm	Stainless Steel	OJ500-M1K	830 mm	
				OCT500-M1A	830 mm	
				OCT300-M1K	308 mm	
				VL18LL	not compatible	