

# Photoelectric slot sensor

# GL5-U/45a/59/115e

- Miniature design
- Optimized for the detection of small parts
- High switching frequency
- Simple and fast mounting
- Clearly visible LED functional display

Miniature slot sensor for small part detection, U design, 5 mm slot width, infrared light, NPN output, dark on, 150 mm fixed cable with JST plug, 3-pin




#### **Function**


The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.


#### Application

- Detection of lead frames
- · Detection of cam positions
- · Detection of limit positions of moving objects
- · Position detection of wafer cases









## **Technical Data**


General specifications					
Light source		IRED			
Light type		Infrared, continuous light , 940 nm			
Target size		0.8 x 1.8 mm			
Slot width		5 mm			
Slot depth		8.5 mm			
Ambient light limit		1000 Lux			
Functional safety related parameters					
MTTF <sub>d</sub>		3760 a			
Mission Time (T <sub>M</sub> )		20 a			
Diagnostic Coverage (DC)		0 %			
Indicators/operating means					
Function indicator		red LED lights up when receiving the light beam			
Electrical specifications					
Operating voltage	UB	5 24 V DC , class 2			
No-load supply current	I <sub>0</sub>	max. 20 mA			
Time delay before availability	t <sub>v</sub>	< 2 ms			
Output					
Switching type		dark-on			
Signal output		1 NPN, overvoltage protected			
Switching voltage		max. 30 V DC			
Switching current		max. 50 mA, resistive load			
Voltage drop	$U_d$	max. 0.2 V at 10 mA max. 0.6 V at 50 mA			

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Technical Data		
Technical Data		
Switching frequency	f	max. 5 kHz
Response time		40 μs Light beam is not interrupted 80 μs Light beam is interrupted
Repeat accuracy	R	0.03 mm
Compliance with standards and directives		
Directive conformity		
EMC Directive 2004/108/EC		EN 60947-5-2:2007+A1:2012
Standard conformity		
Standards		UL 60947-5-2
Approvals and certificates		
UL approval		cULus Recognized, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-30 80 °C (-22 176 °F)
Pollution degree		2
Mechanical specifications		
Degree of protection		IP50
Connection		0.15 m cable with 3-pin JST connector
Material		
Housing		PBT
Mass		3 g
Tightening torque, fastening screws		0.6 Nm
Dimensions		
Height		25.4 mm
Width		7 mm
Length		26.2 mm
Cable length		0.15 m

# **Connection Assignment**



Connection



 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Gr

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com




#### Connection

Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	BU	(blue)
3	BK	(black)

### **Technical Features**



**Response frequency** The response frequency is the value when the disc is rotated, see figure.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



4