

RFID Transponder

IPC02-16



- Battery-free code carrier
- 40 bit fix code
- Readable from both sides
- Degree of protection IP68


Code carrier



Application

The transponder can be read from either side.

Dimensions



Technical Data

General specifications

Operating frequency	125 kHz
Transfer rate	2 kBit/s

Memory

Chip Type	EM4102 Unique (EM Microelectronic)
Read cycles	unlimited
Data retention period	> 10 years

Directive conformity

Radio equipment	
Directive 2014/53/EU	EN 300330
RoHS	
Directive 2011/65/EU (RoHS)	IEC/EN 63000

Standard conformity

Degree of protection	EN 60529
RFID	ISO/IEC 18000-2

Ambient conditions

Ambient temperature	-25 ... 85 °C (-13 ... 185 °F)
Storage temperature	-25 ... 100 °C (-13 ... 212 °F)

Mechanical specifications

Degree of protection	IP68
----------------------	------

Release date: 2025-07-28 Date of issue: 2025-07-28 Filename: 112426_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Technical Data

Material	
Housing	Epoxy (black)
Installation	
On metal	yes
In air	yes
Dimensions	
Height	3 mm
Diameter	16 mm
Construction type	Cylindrical

Read distance in air IPC02-16



- 1

IPH-18GM-V1
- 2

IPH-30GM-V1
- 3

IPH-F61
- 4

IPH-L2-V1
- 5

IPH-FP-V1
- 6

IPH-F15-V1
- 7

IPT1-FP-V1