


# Inductive sensor


## NMB6-F104M-E1-FE-200MM-V3



- Sensing range 6 mm
- Ferrous targets
- Stainless steel sensing face
- 200 mm M8 male cordset with PUR jacket
- Power and output LEDs



### Dimensions



### Technical Data

General specifications		
Switching function		Normally closed (NC)
Output type		NPN
Rated operating distance	$s_n$	6 mm
Installation		flush
Assured operating distance	$s_a$	0 ... 4.86 mm
Actuating element		Ferrous targets
Reduction factor $r_{Al}$		0
Reduction factor $r_{Cu}$		0
Reduction factor $r_{304}$		0.6 ... 0.8
Reduction factor $r_{St37}$		1
Output type		3-wire
Nominal ratings		
Operating voltage	$U_B$	10 ... 30 V DC
Switching frequency	$f$	20 Hz
Hysteresis	$H$	5 ... 15 typ. 10 %
Reverse polarity protection		reverse polarity protected

Release date: 2023-10-27 Date of issue: 2023-10-27 Filename: 915196\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PF** PEPPERL+FUCHS

## Technical Data

Short-circuit protection		yes
Voltage drop	$U_d$	$\leq 2\text{ V}$
Operating current	$I_L$	$\leq 100\text{ mA}$
Current consumption		$\leq 15\text{ mA}$
Off-state current	$I_r$	$\leq 10\text{ }\mu\text{A}$
<b>Indicators/operating means</b>		
Operation indicator		Dual LED Green: power Yellow: output
<b>Standard conformity</b>		
Standards		EN 60947-5-2:2007 IEC 60947-5-2:2007
<b>Approvals and certificates</b>		
UL approval		cULus Listed, General Purpose
CCC approval		CCC approval / marking not required for products rated $\leq 36\text{ V}$
<b>Ambient conditions</b>		
Ambient temperature		$-25 \dots 70\text{ }^\circ\text{C}$ ( $-13 \dots 158\text{ }^\circ\text{F}$ )
<b>Mechanical specifications</b>		
Connection type		fixed cable with plug
Housing material		Stainless steel 1.4305 / AISI 303
Degree of protection		IP67
<b>Connector</b>		
Threading		M8 x 1
Tightening torque		0.4 Nm
Number of pins		3
<b>Cable</b>		
Cable diameter		$4.3\text{ mm} \pm 0.1\text{ mm}$
Bending radius		$> 10 \times$ cable diameter
Material		PUR
Color		black
Number of cores		3
Core cross section		$0.34\text{ mm}^2$
Length	L	200 mm

## Connection



## Connection Assignment



Release date: 2023-10-27 Date of issue: 2023-10-27 Filename: 915196\_eng.pdf

## Connection Assignment

Wire colors in accordance with EN 60947-5-2

1		BN	(brown)
3		BU	(blue)
4		BK	(black)