Ultrasonic sensor UB2000-30GM-E0-V15



Features

- Switch output
- 5 different output functions can be set
- TEACH-IN input
- Synchronisation options

Electrical connection

中

+ U_B

- U_B

Switch output

Teaching input

Sync. input

Standard symbol/Connections:


(version E0, npn)

U

 Φ

Deactivation option

Dimensions



Technical data

General specifications Sensing range Unusable area Standard target plate Transducer frequency Response delay Indicators/operating means LED green LED yellow LED red Electrical specifications Operating voltage No-load supply current I₀ Input Input type

Pulse length

Synchronisation frequency Common mode operation Multiplex operation

Output Output type Repeat accuracy Rated operational current le Voltage drop U_d Switching frequency f Range hysteresis H Temperature influence Standard conformity Standards Ambient conditions Ambient temperature Storage temperature Mechanical specifications Protection degree Connection Material Housing Transducer Mass

200 ... 2000 mm 0 ... 200 mm 100 mm x 100 mm approx. 175 kHz

"Power on", TEACH-IN function object detected indication of the switching state, TEACH-IN function-no object detected "Error", object uncertain

20 ... 30 V DC , ripple 10 $\%_{SS}$ \leq 60 mA

approx. 145 ms

1 TEACH-IN input, operating distance 1: -U_B ... (-U_B +2 V), operating distance 2: (+U_B -2 V) ... +U_B 1 synchronous input level 0: -U_B ... (-U_B + 1 V), level 1: (-U_B + 5 V) ... +U_B Input impedance 27 kOhm Synchronisation pulse: \geq 100 μ s Synchronisation pulse pause: \geq 100 μ s

CE

 $\leq 40~Hz$ $\leq 40/n~Hz$, n = number of sensors

1 switch output E0/E1, npn, normally open/closed, programmable \leq 1 % 200 mA , short-circuit/overload protected \leq 3 V max. 3.4 Hz \leq 1 % of the set operating distance 0.17 % / K

EN 60947-5-2

-25 ... 70 °C (248 ... 343 K) -40 ... 85 °C (233 ... 358 K)

IP65 connector V15 (M12 x 1), 5 pin

brass, nickel-plated, plastic components PBT epoxy resin/hollow glass sphere mixture; polyurethane foam 145 g

2005-07-27

Connector V15



Subject to reasonable modifications due to technical advances

Copyright Pepperl+Fuchs, Printed in Germany

Model number

UB2000-30GM-E0-V15

Function

Synchronization

The sensor features a synchronization input for the suppression of mutual interference. It can be synchronized by applying a square wave voltage. The falling edge of a synchronization pulse at the synchronization input starts a measuring cycle. A low level > 1 s or an open synchronization input will result in the non-synchronized normal operation of the sensor. A high level at the synchronization input disables the sensor. Synchronization cannot be performed during TEACH-IN and vice versa.

Two operating modes are possible:

- The sync. inputs of 2... 5 Sensors are connected with each other. The sensors synchronize themselves and operate cyclically (multiplex mode).
- 2. Multiple sensors can be controlled by the same synchronization signal. The sensors are synchronized.
- The synchronization pulses are sent cyclically to individual sensors. The sensors operate in multiplex mode.

In case of synchronized operation, the response time of the sensor increases due to a longer measuring cycle time caused by synchronization.

Note:

If the option for synchronization is not used, the synchronization input has to be connected to ground (0V) or the sensor has to be operated via a V1 cable connector (4-pin).

Setting the switching points


The ultrasonic sensor features a switch output with two teachable switching points. These are set by applying the supply voltage -UB or +UB to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. Switching point A1 is taught with -UB, A2 with +UB.

Five different output functions can be set:


Function	TEACH-IN procedure			
Window mode, close function	 Set object to near switching point Teach switching point A1 with -UB Set object to far switching point Teach switching point A2 with +UB 			
Window mode, open function	 Set object to near switching point Teach switching point A2 with +UB Set object to far switching point Teach switching point A1 with -UB 			
1 switching point, close function	 Set object to near switching point Teach switching point A2 with +UB Cover sensor or remove all objects from sensing range Teach switching point A1 with -UB 			
1 switching point, open function	 Set object to near switching point Teach switching point A1 with -UB Cover sensor or remove all objects from sensing range Teach switching point A2 with +UB 			
Detection of object presence	 Cover sensor or remove all objects from sensing range Teach switching point A1 with -UB Teach switching point A2 with +UB 			

Characteristic curves/additional information


Characteristic response curve







LED-Window



Copyright Pepperl+Fuchs, Printed in Germany

Default setting of switching points: A1 = blind range, A2 = nominal distance

Displays in dependence on operat-	Green LED	Red LED	Yellow LED
ing mode			
Teach switching point			
Object detected	Flashing	Off	Off
No object detected	Flashing	Off	On
Object uncertain (TEACH-IN invalid)	Off	Flashing	Off
Normal operation	On	Off	Switching state
Interference (e.g. compressed air)	Off	Flashing	Previous state

Mounting conditions

If the sensor is installed in places where the operating temperature can fall below 0 °C, the BF30, BF30-F or BF 5-30 fixing clamp must be used.

Copyright Pepperl+Fuchs, Printed in Germany