





Optical data coupler LS682-DA-EN/F2



- Independent of Ethernet protocol
- TCP/IP, PROFINET, PROFIsafe, EtherCAT, FSoE, EtherNet/IP™, Ethernet POWERLINK etc.
- Plug connection for fast mounting
- No parameterization
- Line indicator for signal strength


Optical data coupler for fast Ethernet, 150 m detection range, red light, 100 Mbit/s data rate, M12 plug



Function

The optical data coupler serves as a connection of Ethernet modules to remote modules. These can move along an axis toward each other. The devices are optimized for conditions in high bay warehouses bays.
The physical transfer takes place protocol-free with 100 MBit/s full duplex. The data rate remains constant irrespective of distance. Telegrams are not saved, which enables immediate transfer.

Dimensions




Technical Data

General specifications		
Effective detection range		0 ... 150 m
Threshold detection range		180 m
Light source		laser diode
Light type		modulated visible red light
Laser nominal ratings		
Note		VISIBLE LASER RADIATION , DO NOT VIEW DIRECTLY WITH OPTICAL INSTRUMENTS
Laser class		1M
Wave length		660 nm
Beam divergence		15 mrad
Pulse length		8 ns
Repetition rate		62.5 MHz
Maximum optical power output		60 mW
Diameter of the light spot		1.5 m at a distance of 100 m
Opening angle		1 °
Ambient light limit		> 10000 Lux
Functional safety related parameters		
MTTF _d		58.6 a
Mission Time (T _M)		10 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		


Technical Data

Data flow indicator		LED green: OPTO-Link LED yellow: LAN-Link LED red: ERROR
Function indicator		Signal strength (8 LED: Red, yellow, green)
Electrical specifications		
Operating voltage	U _B	18 ... 30 V DC
No-load supply current	I ₀	200 mA
Interface		
Interface type		Ethernet; 100 BASE-TX
Physical		M12, D-coded
Protocol		PROFINET EtherNet/IP EtherCAT® Ethernet <i>POWERLINK</i> PROFIsafe
Transfer rate		100 MBit/s (Fast Ethernet)
Output		
Stability alarm output		1 PNP, inactive when falling short of the operating reserve , short-circuit protected, max. 200 mA
Conformity		
Laser safety		EN 60825-1:2014
Approvals and certificates		
UL approval		cULus Listed
FDA approval		IEC 60825-1:2014 Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3 as described in Laser Notice 56, dated May 8, 2019.
Ambient conditions		
Ambient temperature		-10 ... 50 °C (14 ... 122 °F)
Storage temperature		-20 ... 70 °C (-4 ... 158 °F)
Mechanical specifications		
Degree of protection		IP65
Material		
Housing		ABS / PC
Optical face		plastic
Mass		700 g
Dimensions		
Height		90 mm
Width		170 mm
Length		171 mm

Connection Assignment




Assembly



Characteristic Curve

Characteristic response curve




Additional Information

Product Description

The LS682-DA-EN is a device for serial data transfer in Ethernet systems. One F1 and one F2 device is needed for each data transfer link.
Data is transferred in both directions simultaneously by means of modulated light.

Function Displays/Excess Gain

A red alignment LED, which can be seen from a long way off, is located on the front of the device to serve as an alignment aid. As soon as a receiver detects the emitted light of the device opposite it, the flashing frequency of the alignment aid decreases. If the light goes out, this indicates that the devices are aligned with sufficient excess gain. For fine adjustment, the optical data coupler features a bar graph display (signal display) for optimum alignment.



Mounting

The device is mounted using appropriate accessories, e.g., OMH-LS610-01 for wall mounting.
The x-y adjuster is delivered preassembled. It is fixed in the required beam direction ($\pm 90^\circ$ rotation possible) on the mounting bracket.

Release date: 2026-09-02 Date of issue: 2026-09-02 Filename: 265351_eng.pdf